



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Centerline (Pitch): **5 mm [.197 in]**

Number of Rows: **2**

Features

Product Type Features

Block Type	PCB Mount
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stacked Levels	Level 1/Level 2
Closed End	Without
Stacking Configuration	Side Stackable
Number of Positions	3
Number of Rows	2
Wire Entry Angle	Side

Electrical Characteristics

Current Rating (Max)	17.5 A
Voltage Rating	300 VAC



Body Features

Interlock	With
-----------	------

Contact Features

Contact Mating Area Plating Material	Tin
Contact Mount	Through Hole
Contact Base Material	Brass
Contact Current Rating (Max)	17.5 A

Mechanical Attachment

Screwless Terminal Block	No
Mounting Angle	Vertical
Screw Size	M3
Screw Plating Material	Nickel
Screw Material	Brass
Screw Flange	Without
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Blue
Housing Material	PA 66
Centerline (Pitch)	5 mm[.197 in]

Dimensions

PCB Tail Length	3.8 mm[.15 in]
Wire Size	.05 – 3 mm²

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Marking Color	Black
---------------	-------

Packaging Features

Packaging Method	Box
Packaging Quantity	175



Other

Comment	15A Field Wiring
---------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.8% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 282888-3
TERMI-BLOK PCB MOUNT 1&2 3P. 5



TE Part # 796692-3
TERMI-BLOK PCB MOUNT 1&2 3P.5



Customers Also Bought



TE Part #3-644454-1
Polyester Vertical PCB Header: 2.54 mm, Breakaway, MTA 100



TE Part #5-1622824-4
Thick Film Resistor: Current Sense



TE Part #5179160-3
Free Height Receptacle Conn: Board-Board, Vertical, 80, 0.8mm



TE Part #5-103671-4
5 Pos Rt Angle MTE Hdr w/o Latching



TE Part #1622805-7
SIL 8PIN 4RES 10K 5%



TE Part #2-1622805-9
SIL 8PIN 4RES 22K 5%



TE Part #1825010-1
ASE2204=DPDT AUTOSLIDE



TE Part #E62580-000
TAT-125-3/4-0-2.5IN



TE Part #1-2271743-0
AMPMPDU PIN HDR 2.54PITCH 2ROW SMT



TE Part #2271646-6
AMPMODU, REC, 2.54, DR, SMT, 9.90 H, 6POS

Documents

Product Drawings
TERMI-BLOK PCB MOUNT 1&2 3P. 5

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_796691-3_C.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_796691-3_C.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_796691-3_C.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English