




Terminals & Splices > Ring Terminals & Spade Terminals > AMPOWER TERMINAL CENTERLINE 2 HOLES



Terminal & Splice Type: **Rectangular Tongue**

Wire Size: **450000 – 550000 CMA**

Ring & Spade Stud Size: **3/8**

Stud Diameter: **10.31 mm [.406 in]**

Tongue Thickness: **10.67 mm [.42 in]**

[All AMPOWER TERMINAL CENTERLINE 2 HOLES \(5\)](#)

Features

Product Type Features

Ring & Spade Stud Size	3/8
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Copper

Configuration Features

Number of Holes	2
Terminal Angle	Straight

Body Features

Inspection Slot	No
Ring & Spade Plating Material	Tin

Contact Features

Terminal & Splice Type	Rectangular Tongue
Ring & Spade Terminal Orientation	Offset

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------



Dimensions

Wire Size	450000 – 550000 CMA
Stud Diameter	10.31 mm[.406 in]
Tongue Thickness	10.67 mm[.42 in]
Ring & Spade Overall Length	106.68 mm[4.193 in]
Barrel Inside Diameter	26.16 mm[1.03 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	25
Ring & Spade Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 46755-2
HYP8 AMPOWER 500MCM DIE SET

Also in the Series | AMPOWER



Bus Bar Connectors(13)



Ring Terminals & Spade Terminals(141)

Customers Also Bought



TE Part #206138-8
CPC CABLE CLAMPS



TE Part #212007-1
CONTACT PIN ASSY, SZ 8




TE Part #193991-4
PIN ASSY. TPE XII



TE Part #201501-1
SPIROL PIN





TE Part #823355-000
382A034-3/42-0



TE Part #208063-5
SKT ASSY,36 POSN,METRIMATE



TE Part #208062-8
PIN ASSY,36 P,MMATE LF



TE Part #1618060-4
1100-21X=WILMAR OVERCURRENT RE



TE Part #200277-4
BLOCK,50 POSN,M SERIES



TE Part #193990-2
SKT ASSY,TYPE XII, #8 AWG

Documents

Product Drawings

TERM,AMPWR 500MCM HD (2)3/8

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_55831-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_55831-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_55831-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPOWER Terminals and Splices Flyer

English