




Connectors > Power Connectors > Circular Power > Circular Power Connectors



Connector Product Type: **Connector Assembly**

Operating Voltage: **250 VDC**

Connector System: **Wire-to-Board**

Number of Positions: **8**

Sealable: **No**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector & Housing Type	Plug
Circular Connector Shell Type	All Plastic

Configuration Features

Number of Positions	8
Number of Power Positions	0
Number of Signal Positions	8

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Reverse Gender	No
Contact Type	Socket
Contact Current Rating (Max)	7.5 A
Contact Protection	With

Termination Features



Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Panel Mount Feature Type	Flange
Connector Mounting Type	Board Mount
Mating Alignment	With
Mating Retention	With
Panel Mount Feature	With
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling

Housing Features

Housing Color	Black
Housing Material	Thermoplastic
Circular Connector Shell Size	11

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Bag
Packaging Quantity	40

Other

Position Locations Omitted	1, 2
----------------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)
Candidate List Declared Against: JUN 2016 (169)
SVHC > Threshold:
Not Yet Reviewed

Halogen Content

Not Yet Reviewed for halogen content


Solder Process Capability


Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | AMP CPC

 Circular Connector Adapters(7)	 Circular Connector Boots & Strain Relief(6)	 Circular Connector Caps & Covers(16)	 Circular Connector Hardware(3)
 Circular Connector Keying Plugs(2)	 Circular Connector Seals(36)	 Circular Power Connectors(513)	 Insertion & Extraction Tools(1)



Power Contacts(5)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Customers Also Bought



TE Part #206036-4
CPC SERIES 6 TWO-PIECE



TE Part #206153-2
CPC SERIES 6




TE Part #HDT-04-08
CRIMP TOOL, HDT-04-08




TE Part #4-881545-2
AMP SHUNT ASS'Y




TE Part #282847-5
TERMI-BLOK PCB MOUNT 35 SP.5



TE Part #1825068-2
C22204 CAP RED



TE Part #4-1625984-7
Power Resistors: Aluminum Housed, HSA



TE Part #284047-5
TERMI-BLOK VERTICAL PLUG STACK



TE Part #1676288-2
RN 0805 2K37 0.1% 10PPM 1KRL



TE Part #1676306-2
RN 0805 332R 0.1% 10PPM 1KRL

Documents

Product Drawings

CPC PLUG ASSY SIZE 11-8,POSTED

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_796902-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_796902-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_796902-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Circular Plastic Connector With Type III+ Contacts

English

Engineering Report

English