




Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Top & Side**

Hood & Base Locking Device Type: **Screwlock**

Features

Product Type Features

Hood & Base Connector Product Type	Hood
------------------------------------	------

Body Features

Color	Black
Cable Entry Location	Top & Side

Mechanical Attachment

Hood & Base Locking Device Type	Screwlock
---------------------------------	-----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content



Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

			
TE Part # T1936320000-000 H32BPR-AG-4S	TE Part # T2193503101-000 HCM350-MC	TE Part # T0924048581-000 H32BRP-4P-350-FRAME	TE Part # T3609500102-000 DLX-50-M

Customers Also Bought

			
TE Part #1-480708-9 12P UMNL PLUG HSG BLK	TE Part #5-1415073-1 RT3S4R24	TE Part #T1610062120-000 H6B-SGRS-M20	TE Part #1-917657-5 DYNAMIC 3200 HDR ASSY

			
TE Part #640250-1 3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156	TE Part #1473203-1 TH/.025 CONNECTOR SYSTEM, HOUSING	TE Part #T0931003003-000 CODING-PIN-M3	TE Part #170221-3 TAB WITH LANCE FOR M.I.C.



Documents

Product Drawings  
H32BPR-TGXH-4S-M50

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_T1926320150-001\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_T1926320150-001\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_T1926320150-001\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English

Application Specification