

HD36-18-14SN-059 ✓ ACTIVE

DEUTSCH | DEUTSCH HD, DEUTSCH HD30


TE Internal #: HD36-18-14SN-059

Hybrid, Housing for Female Terminals, Wire-to-Wire, 14 Position, Sealable, Wire & Cable, 13A Contact Current Rating (Max), Power & Signal

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Housings > DEUTSCH HD30 HOUSINGS



Connector & Housing Type: **Housing for Female Terminals**

Mating Pin Diameter: **1.59 mm [.063 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **14**

Sealable: **Yes**

[All DEUTSCH HD30 HOUSINGS \(327\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	Contact Retainer
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Blank Cavity Position	0
Number of Positions	14

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V



Body Features

Cable Exit Angle	180°
Body Material	Aluminum

Contact Features

Mating Pin Diameter	1.59 mm[.063 in]
Contact Current Rating (Max)	13 A

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	Add By Accessory
Mating Alignment Type	Polarized

Dimensions

Product Width	42.97 mm[1.692 in]
Product Length	77.7 mm[3.059 in]
Product Height	42.97 mm[1.692 in]
Accepts Wire Insulation Diameter Range	2.54 – 3.4 mm[.1 – .134 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Degree of Protection	IP67
----------------------	------

Packaging Features

Packaging Quantity	100
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-D48-ST273
DEUTSCH SOLID CONTACTS

TE Part # 0411-204-1605
EXT TOOL, SIZE 16, 16-18 AWG, N,
DRK BLU

TE Part # CAT-H3930-CH8172
DEUTSCH HD30 HOUSINGS

TE Part # CAT-D48-SFT273
DEUTSCH STAMPED & FORMED
CONTACTS

TE Part # CAT-D48-SP729
DEUTSCH SEALING PLUGS





TE Part # CAT-H3930-PC8382
DEUTSCH HD30 PLUG PROTECTIVE
CAPS

TE Part # 0411-291-1405
EXT TOOL, SIZE 16, 14-16 AWG, N,
GRN



TE Part # HD30-18BT-BK
BOOT, 18SZ, ST, BLK



Also in the Series | DEUTSCH HD



Also in the Series | DEUTSCH HD30





Other Automotive Connector Accessories(6)

Customers Also Bought



TE Part #0462-221-1631
DEUTSCH SOLID CONTACTS



TE Part #114021-ZZ
DEUTSCH HD30 MOUNTING HARDWARE




TE Part #WB-48SA
DEUTSCH DRB WEDGELOCKS




TE Part #114019-ZZ
DEUTSCH SEALING PLUGS



TE Part #1060-16-0988
DEUTSCH STAMPED & FORMED CONTACTS



TE Part #0526-012-0090
RET BOLT, M5, AG, DRC26



TE Part #1010-069-0306
FRONT SEAL

Documents

Product Drawings

PLG,14P,AL,N, CBL CLMP BT, DRAIN,16,S,MC

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_HD36-18-14SN-059_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_HD36-18-14SN-059_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_HD36-18-14SN-059_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English