




Connectors > Rectangular Connectors > Rectangular Contact Inserts



Contact Insert Pole Configuration: 4

Number of Positions: 4

Sealable: No

Contact Current Rating (Max): 1 A

Circuit Application: Signal

Features

Product Type Features

Product Type	Contact Insert
Sealable	No

Configuration Features

Number of Positions	4
---------------------	---

Contact Features

Contact Insert Pole Configuration	4
Contact Current Rating (Max)	1 A

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1500063000-000
H6B-AG



TE Part # T1010062100-000
H6B-KDBP




TE Part # T2114000101-000
HMN-USB-M




TE Part # T2070064201-000
H6BN-T2-F

Also in the Series | HDC HMN




Connector Contacts(2)



Insertion & Extraction Tools(1)



Rectangular Connector Hardware(16)



Rectangular Contact Inserts(111)

Customers Also Bought





TE Part #1672125-5
DP CONTACTORS, 1 POLE



TE Part #2273107-1
M12 A-CODE Y-CABLE ASSEMBLY



TE Part #2273111-5
M8 FS - M12 MS CABLE ASSY BL



TE Part #9-1879352-8
RR02 5% 3K6 AMMO



TE Part #T1770063121-000
H6B-TBFH-PG21



TE Part #T2070011013-000
DAM-13



TE Part #T1236240150-000
H24B-XWTSH-M50



TE Part #T1220240140-000
H24B-TG-M40



TE Part #2-292175-6
CT Box Header SMT: Vert, Shrouded



TE Part #T3707210101-000
DLX-21-MSD (13-18)

Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T2114000201-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T2114000201-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T2114000201-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

- Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English



Product Specifications

Product Specification

English