



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Backshells & Clamps



Backshell & Clamp Accessory Type: **Cable Gland**

Sealable: **Yes**

Features

Product Type Features

Backshell & Clamp Accessory Type	Cable Gland
Sealable	Yes

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Pb (1.9% in Pb-Alloy in Copper) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # T3609110101-000 DLX-11-MS	 TE Part # T3609110111-000 DLX-11-MTS	 TE Part # T3609110121-000 DLX-11-MSN
---	---	--

Customers Also Bought

 TE Part #205163-5 RECEPT ASSY,15 POSN,AMPLIMITE	 TE Part #6-146490-6 32 MODII HDR DRST UNSHRD STKG	 TE Part #2-1879645-6 H8 33R2 0.5% 50PPM	 TE Part #YACT24MA98SNC00100 JAM NUT RECEPTACLE
 TE Part #2102317-2 Fortis Zd 10 Col R/A Right Assy SE	 ANVIL REPRESENTATION ONLY TE Part #3-1803057-7 ANVIL, COMBINATION	 ANVIL REPRESENTATION ONLY TE Part #5-1803171-0 ANVIL	 CRIMPER REPRESENTATION ONLY TE Part #9-1633962-5 CRIMPER, INSULATION F PREMIUM



Documents

Product Drawings

BLIND-11-MS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T3165110101-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T3165110101-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T3165110101-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English