



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Hood & Base Locking Device Type: **Screwlock**

Sealable: **Yes**

Features

Product Type Features

Product Size	3
Hood & Base Connector Product Type	Base Housing
Sealable	Yes

Body Features

Material	Die Cast Aluminum
----------	-------------------

Mechanical Attachment

Locking Device Location	Hood
Hood & Base Locking Device Type	Screwlock

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # T1912061116-000 H6BPR-TSHC-PG16	 TE Part # T1912061120-000 H6BPR-TSHC-M20	 TE Part # T1912061121-000 H6BPR-TSHC-PG21	 TE Part # T1912061125-000 H6BPR-TSHC-M25
 TE Part # T1912062125-000 H6BPR-TSHC-M25	 TE Part # T1912062125-001 H6BPR-TSHC-M25	 TE Part # T1922061116-000 H6BPR-TGHC-PG16	 TE Part # T1922061120-000 H6BPR-TGHC-M20





TE Part # T1922061121-000
H6BPR-TGHC-PG21



TE Part # T1922061125-000
H6BPR-TGHC-M25



TE Part # T1922061129-000
H6BPR-TGHC-PG29



TE Part # T1922061132-000
H6BPR-TGHC-M32



TE Part # T1922062125-000
H6BPR-TGHC-M25

Customers Also Bought



TE Part #206429-1
CPC SERIES 6



TE Part #0462-209-16141
DEUTSCH SOLID CONTACTS



TE Part #206966-7
CPC CABLE CLAMPS



TE Part #W6P
DEUTSCH DT WEDGELOCKS



TE Part #114017-ZZ
DEUTSCH SEALING PLUGS



TE Part #1-480698-0
02P UMNL PLUG HSG NATL

Documents

Product Drawings
H6BPR-AGC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T1932061000-000_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_T1932061000-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1932061000-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English

Application Specification