



M12 Connector

TE Internal #: T4140012081-000

M12 Connector, Standard Circular Connectors, Wire-to-Panel, 8 Position, Sealable, Printed Circuit Board, 2A Contact Current Rating (Max), Signal

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > M12 Panel Mount PCB



Connector System: **Wire-to-Panel**
Number of Positions: **8**
Sealable: **Yes**
Connector & Contact Terminates To: **Printed Circuit Board**
Contact Current Rating (Max): **2 A**

[All M12 Panel Mount PCB \(112\)](#)

Features

Product Type Features

Product Type	Connector
Accessory Color	Black
Assembly Type	Electrical Connector
Connector System	Wire-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board
Circular Connector Type	Plug
Shell Type	Metal

Configuration Features

Keying & Polarized Position Locations	A
Factory Installed Backshell	No
Keying	A
Number of Positions	8



Number of Power Positions	0
Number of Signal Positions	8
Contacts Preloaded	Yes

Electrical Characteristics

Operating Voltage	30 VAC
-------------------	--------

Body Features

Peripheral Seal Material	Silicone
Environmental Protection	IP67
O-Ring Material	Silicone
Environmental Protection Type	Elastomer Sealed
Shell Plating Material	Nickel
Shell Base Material	Copper Alloy
Circular Connector Insulation Material Type	Polyamide 66 GF25

Contact Features

Contact Current Rating (Max)	2 A
Reverse Gender	Yes
Circular Connector Contact Type	Pin

Mechanical Attachment

Polarization Code	A
Mating Alignment Type	Keyed

Housing Features

Circular Connector Shell Size	18
-------------------------------	----

Usage Conditions

IP Water Sealing Level	IP67
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	HB
------------------------	----

Packaging Features

--	--



Packaging Quantity	1
--------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (4% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C73765-M1E
M12 Field Installable Unshielded

Also in the Series | M12 Connector



Circular Connector Adapters(2)



Standard Circular Connectors(453)

Customers Also Bought



TE Part #1-2328724-3
0.3mm FPC Connectors



TE Part #1-2823448-3
M12 STRAIGHT CRIMPED STRAIN RELIEF



TE Part #1-34142-1
PG R 22-16 COMM 22-18 MIL 6



TE Part #1-480700-4
03P UMNL PLUG HSG YELL



TE Part #1-2176340-6
CRGCQ 0603 330R 5%




TE Part #1-2176327-4
CRGP 0805 120R 1%



TE Part #1-2176311-2
RP 1E 0.1W 1K5 0.1% 25PPM 1K RL



TE Part #1318750-2
HIGH PIN COUNT HEADER



TE Part #1318756-2
TH/.025 CONNECTOR SYSTEM, HOUSING



TE Part #T4143412041-000
M12 Panel Mount PCB

Documents

Product Drawings

M12,REAR MOUNT,MALE,A,8P,SOLDER PCB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T4140012081-000_B.2d_dxf.zip

T4140012081-000

M12 Connector, Standard Circular Connectors, Wire-to-Panel, 8 Position, Sealable, Printed Circuit Board, 2A Contact Current Rating (Max), Signal



English

Customer View Model

[ENG_CVM_CVM_T4140012081-000_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T4140012081-000_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

[M12 PCB/Panel Connectors 8/12Pin](#)

English

Product Specifications

[Application Specification](#)

English