



M12 Connector

TE Internal #: T4140512041-000

M12 Connector, Standard Circular Connectors, Wire-to-Panel, 4 Position, Sealable, Printed Circuit Board, 4A Contact Current Rating (Max), Signal

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > M12 Panel Mount PCB



Connector System: **Wire-to-Panel**  
Number of Positions: **4**  
Sealable: **Yes**  
Connector & Contact Terminates To: **Printed Circuit Board**  
Contact Current Rating (Max): **4 A**

[All M12 Panel Mount PCB \(112\)](#)

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| Product Type                      | Connector             |
| Accessory Color                   | Black                 |
| Assembly Type                     | Electrical Connector  |
| Connector System                  | Wire-to-Panel         |
| Sealable                          | Yes                   |
| Connector & Contact Terminates To | Printed Circuit Board |
| Circular Connector Type           | Plug                  |
| Shell Type                        | Metal                 |

Configuration Features

|                                       |    |
|---------------------------------------|----|
| Keying & Polarized Position Locations | D  |
| Factory Installed Backshell           | No |
| Keying                                | D  |
| Number of Positions                   | 4  |



|                            |     |
|----------------------------|-----|
| Number of Power Positions  | 0   |
| Number of Signal Positions | 4   |
| Contacts Preloaded         | Yes |

Electrical Characteristics

|                   |         |
|-------------------|---------|
| Operating Voltage | 250 VAC |
|-------------------|---------|

Body Features

|                                             |                   |
|---------------------------------------------|-------------------|
| Peripheral Seal Material                    | Silicone          |
| Environmental Protection                    | IP67              |
| O-Ring Material                             | Silicone          |
| Environmental Protection Type               | Elastomer Sealed  |
| Shell Plating Material                      | Nickel            |
| Shell Base Material                         | Copper Alloy      |
| Circular Connector Insulation Material Type | Polyamide 66 GF25 |

Contact Features

|                                 |     |
|---------------------------------|-----|
| Contact Current Rating (Max)    | 4 A |
| Reverse Gender                  | Yes |
| Circular Connector Contact Type | Pin |

Mechanical Attachment

|                   |   |
|-------------------|---|
| Polarization Code | D |
|-------------------|---|

Housing Features

|                               |    |
|-------------------------------|----|
| Circular Connector Shell Size | 18 |
|-------------------------------|----|

Usage Conditions

|                             |                                         |
|-----------------------------|-----------------------------------------|
| IP Water Sealing Level      | IP67                                    |
| Operating Temperature Range | -40 – 85 °C[-40 – 185 °F][-40 – 185 °F] |

Operation/Application

|                     |        |
|---------------------|--------|
| Circuit Application | Signal |
| Shielded            | No     |

Industry Standards

|                        |    |
|------------------------|----|
| UL Flammability Rating | HB |
|------------------------|----|

Packaging Features

|                    |   |
|--------------------|---|
| Packaging Quantity | 1 |
|--------------------|---|



Other

|                   |    |
|-------------------|----|
| Field Serviceable | No |
|-------------------|----|

Product Compliance

For compliance documentation, visit the product page on TE.com>



|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                            |
|-----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                                                                                                                                                                                                                                                                                                                                                                                  |
| EU ELV Directive 2000/53/EC                   | Compliant with Exemptions                                                                                                                                                                                                                                                                                                                                                                                                  |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>SVHC > Threshold:<br>Pb (4% in Component Part)<br><b>Article Safe Usage Statements:</b><br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                                                                                                                                                                                                                                                                                                        |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                                                                                                                                                                                                                                                                                                               |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                                              |                                |                                |                                |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|--------------------------------|
|  <div>TE Part # CAT-C73765-M1E<br/><a href="#">M12 Field Installable Unshielded</a></div> | <div>TE Part # 2355080-1</div> | <div>TE Part # 2355080-2</div> | <div>TE Part # 2355080-3</div> |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|--------------------------------|



Also in the Series | M12 Connector



Circular Connector Adapters(2)



Standard Circular Connectors(453)

Customers Also Bought



TE Part #120953-6  
UPM EXPANDED RCPT ASSEMBLY



TE Part #1-84982-8  
1MM FFC SMT V ASSY 18P EMBOSS



TE Part #1623475-1  
CRG1206 1% 2K2




TE Part #1-207825-5  
RCPT ASSY,POSTED,SER 1,SZ 11-4




TE Part #T4143512041-000  
M12 Panel Mount PCB



TE Part #1622563-2  
LR1 1% 750K



TE Part #1393310-2  
VCFM-1000=FROM SEC



TE Part #2-1355350-1  
MQS COVER 18POS



Documents

Product Drawings

M12,REAR MOUNTING,MALE,D CODE,4P

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_T4140512041-000\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_T4140512041-000\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_T4140512041-000\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

Product Specifications

Application Specification

English