



STEP-Z

TE Internal #: 5-1761613-5
PCB Mount Receptacle, Vertical, Board-to-Board, 104 Position, 1.3 mm [.051in] Centerline, Gold, Printed Circuit Board, 1A Contact Current Rating (Max)

[View on TE.com >](#)

Connectors > PCB Connectors > Board-to-Board Connectors > Board-to-Board Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**
PCB Mount Orientation: **Vertical**
Connector System: **Board-to-Board**
Number of Positions: **104**
Centerline (Pitch): **1.3 mm [.051 in]**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Rows	18
Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	104
Board-to-Board Configuration	Parallel

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	500 VAC
Insulation Resistance	18 MΩ
Operating Voltage	48 VAC

Contact Features

Contact Layout	Matrix
Mating Tab Width	1 mm[.04 in]
Mating Tab Thickness	.2 mm[.008 in]



Contact Shape & Form	Dual Beam, Single Beam
PCB Contact Termination Area Plating Material	Tin-Silver
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.76 µm[29.9212 µin]
Contact Type	Socket
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Printed Circuit Board	Surface Mount - Solder Ball
---	-----------------------------

Mechanical Attachment

Mating Retention	With
Mating Alignment	Without
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	1.3 mm[.051 in]
Housing Color	Natural
Housing Material	Thermoplastic

Dimensions

Connector Height	10.65 mm[.419 in]
Row-to-Row Spacing	2 mm[.079 in]
Stack Height	15 mm, 17 mm, 18 mm, 20 mm, 25 mm[.984 in]
PCB Thickness (Recommended)	1.57 mm[.8 in]

Usage Conditions

Operating Temperature Range	0 – 100 °C[32 – 212 °F]
-----------------------------	-------------------------

Operation/Application

Assembly Process Feature	None
Circuit Application	Power & Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------



Packaging Features

Packaging Quantity	30
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 6-1761612-0 STEP-Z PLUG 10MM 104P LF ST	TE Part # 6-1761612-3 STEP-Z PLUG 13MM 104P LF ST	TE Part # 6-1761612-5 STEP-Z PLUG 15MM 104P LF ST	TE Part # 6-1761612-2 STEP-Z PLUG 12MM 104P LF ST



TE Part # 7-1761612-0
STEP-Z PLUG 20MM 104P LF ST

Customers Also Bought

TE Part #2170738-1
QSF28, 1X3, CAGE ASSEMBLY,
SPRING, HS

TE Part #2-6450820-0
MBXL VERT HDR 1LP+16S+1LP

TE Part #1645613-2
8P.P.L.TERM.(D)

TE Part #2007863-1
IMP100S,H,V5P16C,RG,LEW39,4.5

TE Part #2042139-2
RA Male Connector, IEC L3

TE Part #2185223-1
ASSY, SEATING TOOL, QSFP

TE Part #2226412-1
ASSY PIN MODULE, 16-02 PCB RA,
STD

TE Part #2299924-1
ZQSFP+ STACKED REC ASSEMBLY
2X3,4LP HS

TE Part #2299940-1
ZQSFP+ STACKED REC ASSEMBLY
2X1,4LP HS

TE Part #7-1761612-0
STEP-Z PLUG 20MM 104P LF ST

Documents

Product Drawings
STEP-Z RCPT 05MM 104P LF ST
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5-1761613-5_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_5-1761613-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1761613-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[STEP-Z Interconnection System](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_5-1761613-5_091220171218_dmtec](#)

English

[MD_5-1761613-5_091220171218_dmtec](#)

English