



CIR

TE Internal #: Y5015-000000009726

CIR, Standard Circular Connectors, Wire-to-Wire / Cable-to-Cable, 35 Position, Wire & Cable, Power & Signal, Panel Mount, Reverse Gender

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > 4 HOLE FLANGE RECEPTACLE REAR PNL FEM.



Connector System: **Cable-to-Cable, Wire-to-Wire**

Number of Positions: **35**

Connector & Contact Terminates To: **Wire & Cable**

Circuit Application: **Power & Signal**

Connector Mounting Type: **Panel Mount**

[All 4 HOLE FLANGE RECEPTACLE REAR PNL FEM. \(9\)](#)

**Features**

**Product Type Features**

Prewired	No
Product Type	Connector
Accessory Color	Black
Connector System	Cable-to-Cable, Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Metal

**Configuration Features**

Factory Installed Backshell	Without
Number of Positions	35
Contacts Preloaded	No

**Electrical Characteristics**

Operating Voltage	700 VAC
-------------------	---------

**Body Features**

Environmental Protection	With
Environmental Protection Type	Sealed



Shell Plating Material	Black Chromate Over Zn Cobalt
Shell Base Material	Aluminum Alloy
Circular Connector Insulation Material Type	Low Fire Hazard Thermoplastic

#### Contact Features

Reverse Gender	Yes
Contact Layout Arrangement	Circular
Circular Connector Contact Type	Socket

#### Mechanical Attachment

Mating Retention Type	Bayonet
Mating Alignment	With
Panel Mount Feature Type	Square Flange
Connector Mounting Type	Panel Mount
Mating Alignment Type	Keyed
Mating Retention	With

#### Housing Features

Circular Connector Shell Size	40
-------------------------------	----

#### Dimensions

Wire Size	12 AWG
-----------	--------

#### Usage Conditions

IP Water Sealing Level	IP67
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

#### Operation/Application

Circuit Application	Power & Signal
Shielded	Yes

#### Packaging Features

Packaging Quantity	10
--------------------	----

#### Other

Position Locations Omitted	All
Field Serviceable	Yes

#### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | CIR



Circular Connector Adapters(16)



Circular Connector Contact Inserts(16)



Circular Connector Hardware(8)



Circular Connector Seals(36)




Insertion & Extraction Tools(4)



Standard Circular Connectors(36)


## Customers Also Bought



TE Part #661269-000  
TXR21AB00-1605AI



TE Part #1617807-5  
FC-335-SY8= RELAY, 3PST



TE Part #358203-000  
Bulbous Heat Shrink Boots: Lipped,  
Straight



TE Part #2-1614894-3  
CPF 0805 301K 0.1% 25PPM 1K RL




TE Part #642427-000  
Heat Shrink Boots: Poly Mold, Lipped



TE Part #1617147-5  
JMGAP-26P = M39016/17-030P



TE Part #1617164-7  
JMACT-5XL = M28776/1-025L



TE Part #358279-000  
382C312-50-01-0



TE Part #ZPF000000000007174  
983-ORS 08-98 PN



TE Part #1617119-5  
J1MAW-18XP = M39016/7-021P

## Documents



### Product Drawings

#### FIXED, REAR MOUNT SOCKET CONNECTOR

French

---

### Datasheets & Catalog Pages

#### CIRP Catalog

English

#### CIRP Catalog

---

### Product Specifications

#### Application Specification

French