



CIR

TE Internal #: Y5015-000000078003

CIR, Circular Connector Adapters, 24 Shell Size, Cable-to-Cable,
Wire & Cable, Power & Signal, Operating Temperature Range -55 –
125 °C [-67 – 257 °F]

[View on TE.com >](#)

Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Adapters >
90 ELBOW HEATSHRINK ADAPT. - TYPE ECHSA



Circular Connector Shell Size: **24**
Connector System: **Cable-to-Cable**
Connector & Contact Terminates To: **Wire & Cable**
Circuit Application: **Power & Signal**
Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**

[All 90 Elbow Heatshrink Adapt. - Type ECHSA \(8\)](#)

Features

Product Type Features

Product Type	Accessory
Accessory Type	Adapter
Connector System	Cable-to-Cable
Connector & Contact Terminates To	Wire & Cable

Body Features

Connector Color	Black
-----------------	-------

Housing Features

Circular Connector Shell Size	24
-------------------------------	----

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	50
--------------------	----



Other

Adapter Type	90° Angled
Comment	Heatshrink

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-R131-C4961G

WIRE SEAL GROMMET - CIRP



Also in the Series | CIR



Circular Connector Adapters(16)



Circular Connector Contact Inserts(16)



Circular Connector Hardware(8)



Circular Connector Seals(36)



Insertion & Extraction Tools(4)



Standard Circular Connectors(36)


Customers Also Bought



TE Part #2-2176244-9
CRGS0805 5% 220R



TE Part #4-2176244-2
CRGS0805 5% 2K7




TE Part #192129-1
4MM 10B1S1/4-X 10-32




TE Part #YDTS26Z25-19PNC001
D38999: Straight Plug, 25-19 Insert



TE Part #1483353-1
MICRO-MATCH LEAD 10P 100MM



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #160808-2
250 FASTON,REC.,17-14 AWG,BR



TE Part #1587902-9
Plug Pig Tail Assy, HV, HVA280 2P



TE Part #2-1393253-3
W68-X2Q110-25V=M6/M7/M9/W6/W7



TE Part #1483358-3
MICRO-MATCH LEAD 20P 250MM



Documents

Product Drawings

90 DEGREE HEATSHRINK SCREEN ADAPTOR

French

Datasheets & Catalog Pages

CIRP Catalog

English

CIRP Catalog