



CIRH

TE Internal #: Y5015-000000100130

CIRH, Standard Circular Connectors, Wire-to-Wire / Cable-to-Cable, 6 Position, Wire & Cable, Power & Signal, Panel Mount, Reverse Gender

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > 4 HOLE FLANGE RECEPTACLE REAR PNL FEM.



Connector System: **Cable-to-Cable, Wire-to-Wire**

Number of Positions: **6**

Connector & Contact Terminates To: **Wire & Cable**

Circuit Application: **Power & Signal**

Connector Mounting Type: **Panel Mount**

[All 4 HOLE FLANGE RECEPTACLE REAR PNL FEM. \(17\)](#)

Features

Product Type Features

Product Type	Connector
Accessory Color	Black
Prewired	No
Connector System	Cable-to-Cable, Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Factory Installed Backshell	Without
Number of Positions	6
Contacts Preloaded	No

Body Features

Shell Plating Material	Black Chromate Over Zn Cobalt
Shell Base Material	Aluminum Alloy
Circular Connector Insulation Material Type	Low Fire Hazard Rubber

Contact Features



Reverse Gender	Yes
Contact Layout Arrangement	18 – 12
Circular Connector Contact Type	Socket

Mechanical Attachment

Mating Retention Type	Bayonet
Mating Alignment	With
Panel Mount Feature Type	Square Flange
Connector Mounting Type	Panel Mount
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	18
-------------------------------	----

Usage Conditions

IP Water Sealing Level	IP67
Operating Temperature Range	-55 – 200 °C[-67 – 392 °F]

Operation/Application

Circuit Application	Power & Signal
Shielded	Yes

Packaging Features

Packaging Quantity	10
--------------------	----

Other

Position Locations Omitted	All
Field Serviceable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)



SVHC > Threshold:
Pb (.15% in Aluminium alloy component)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-R131-C4967L
CRIMP CONTACT PIN - CIRH




TE Part # CAT-R131-C4967M
CRIMP CONTACT SOCKET - CIRH


Also in the Series | CIRH




Circular Connector Contact Inserts(15)



Circular Connector Seals(17)



Standard Circular Connectors(71)



Unscreened Circular Connector Backshells & Clamps(55)

Customers Also Bought



TE Part #2-6609115-3
CORCOM GG SERIES MULTI-FUNCTION INLET FI



TE Part #2-320561-3
PIDG RING TONGUE TERMINALS



TE Part #1879071-2
Power Resistor: Aluminum Housed, 75 Watt



TE Part #204351-1
SZ 22 SOCKET CONTACT



TE Part #120953-4
UPM EXPANDED RCPT ASSEMBLY



TE Part #2029030-2
2P MICRO MNL HDR ASY SR SIDE L



TE Part #1546306-2
2P .374" DR BARRIER STRIP



TE Part #1546306-3
3P .374" DR BARRIER STRIP



TE Part #2029047-2
2P MICRO MNL RCPT HSG SR SIDE



TE Part #Y5015-000000100113
CRIMP CONTACT SOCKET - CIRH

Documents

Product Drawings

FIXED SOCKET CONNECTOR

French

Datasheets & Catalog Pages

CIRH Brochure

English

Product Specifications

Application Specification

French