




Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Receptacle Kit, Cable to Cable, Signal, 1.27 mm



Connector & Housing Type: **Receptacle**

Solid Wire Size: **.05 – .1 mm²**

Shielded: **Yes**

Connector System: **Cable-to-Cable**

[All IDC D-Sub: Receptacle Kit, Cable to Cable, Signal, 1.27 mm \(5\)](#)

Features

Product Type Features

Rails	Without
Connector & Housing Type	Receptacle
Connector System	Cable-to-Cable
Connector Product Type	Connector Kit
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	68
Number of Rows	2
Compatible With Wire & Cable Type	Round Jacketed Cable

Body Features

Color	Black
	.025 in



Cover Material	Thermoplastic
Plug Shell Plating Material	Tin-Nickel Alloy
Plug Shell Material	Steel
Shell Material	Steel
Shell Plating Material	Nickel over Copper

Contact Features

	30 µin
Contact Mating Area Plating Material	Gold, Gold Flash
Contact Underplating Material	Nickel, Palladium Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1 A

Termination Features

Termination Cover Type	Standard
Termination Cover Method	Unassembled
Termination Cover	Without
Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)

Mechanical Attachment

Mating Connector Lock	Without
Mounting Angle	None
Panel Mount Feature	Without
PCB Mount Retention Type	None
Detent	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Thermoplastic
Housing Color	Black
Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Insulation Diameter (Max)	.91 mm
Accepts Wire Insulation Diameter Range	.74 – .89 mm[.029 – .036 in]
Solid Wire Size	.05 – .1 mm²



Wire Size	.05 – .09 mm²
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Shielded	Yes
Circuit Application	Signal
Industry Standards	
UL Flammability Rating	UL 94V-0
Cover Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Kit
Packaging Quantity	360
Other	
Comment	Receptacle connector requires backshell kit for complete assembly

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-020-ADRV127 AMPLIMITE D-Sub Receptacle Assembly: Vertical, 1.27mm	TE Part # CAT-020-DPAV127 D-Sub Plug Assembly: Standard, Vertical, 1.27mm	TE Part # CAT-018-DRARA127 D-Sub Receptacle Assembly: Right Angle, 1.27mm	TE Part # CAT-020-DRAVAP127 D-Sub Receptacle Assembly: Vertical, Action Pin, 1.27mm
TE Part # CAT-AM7-436507 IDC D-Sub: Receptacle Assembly, Panel Mount, Signal, 1.27 mm	TE Part # 5749195-2 68 50SR KIT,ST,UK	TE Part # 5786152-3 68 50SR BKSHL KIT W/JS,UNPNTD,	TE Part # 1-749621-6 68 50S CABLE PLUG CONN/COV KIT
TE Part # 853240-1 STD PLUG & RECPT HOLDER ASSY			

Also in the Series | AMPLIMITE 0.50 Series

D-Sub Backshells & Clamps(31)	D-Sub Covers(20)	D-Sub Locking & Mounting(8)	IDC D-Sub Connectors(77)
--	-------------------------	--	---------------------------------




Insertion & Extraction Tools(1)



PCB D-Sub Connectors(196)

Customers Also Bought



TE Part #1-5750913-7
IDC D-Sub: Connector Kit, Plug, Signal, 1.27 mm



TE Part #1757823-5
AMPLIMITE,ASY,PLUG,STD,90,ZN,5



TE Part #1-1757823-2
AMPLIMITE,ASY,PLUG,STD,90,ZN,6,CT



TE Part #1-350777-2
02P UMNL V0 PLUG HSG RED



TE Part #1-350777-3
02P UMNL V0 PLUG HSG ORANGE




TE Part #103239-3
03 MODII HDR SRST B/A .100CL



TE Part #1-480700-1
03P UMNL PLUG HSG BRN



TE Part #1-750877-9
100 50SR TERMINATOR COVER



TE Part #YDJT16F25-35PCV001
PLUG ASSY

Documents

Product Drawings
68 50SR CABLE RCPT KIT
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5749699-7_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_5749699-7_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5749699-7_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - .050 Series Connector](#)

English

[AMPLIMITE .050 Series D-sub Connectors QRG](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Instruction Sheets

[Customer Manual \(U.S.\)](#)

English