



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Connector Kit, Plug, Signal, 1.27 mm



Connector & Housing Type: **Plug**

Solid Wire Size: **.05 – .1 mm²**

Shielded: **Yes**

Connector System: **Cable-to-Board, Cable-to-Cable**

[All IDC D-Sub: Connector Kit, Plug, Signal, 1.27 mm \(21\)](#)

Features

Product Type Features

Rails	Without
Connector & Housing Type	Plug
Connector System	Cable-to-Board, Cable-to-Cable
Connector Product Type	Connector Kit
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	68
Number of Rows	2
Compatible With Wire & Cable Type	Round Jacketed Cable

Body Features

Color	Black
	.025 in
Cover Material	Polyester
Plug Shell Plating Material	Tin-Nickel Alloy
Plug Shell Material	Steel
Shell Material	Carbon Steel
Shell Plating Material	Tin over Copper



Contact Features

	30 µin
Contact Mating Area Plating Material	Gold, Gold Flash
Contact Underplating Material	Nickel, Palladium Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1 A

Termination Features

Termination Cover Type	Wire Lacing
Termination Cover Method	Unassembled
Termination Cover	Without
Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)

Mechanical Attachment

Mating Connector Lock	Without
Mounting Angle	None
Panel Mount Feature	Without
PCB Mount Retention Type	None
Detent	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Polyester
Housing Color	Black
Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Insulation Diameter (Max)	.91 mm
Accepts Wire Insulation Diameter Range	.81 – .91 mm[.032 – .036 in]
Solid Wire Size	.05 – .1 mm²
Wire Size	.05 – .09 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	Yes
----------	-----



Circuit Application	Signal
Industry Standards	
UL Flammability Rating	UL 94V-0
Cover Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Kit
Packaging Quantity	10
Other	
Comment	Plug connector requires backshell kit for complete assembly

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-020-ADRV127
AMPLIMITE D-Sub Receptacle Assembly: Vertical, 1.27mm

TE Part # CAT-018-DRARA127
D-Sub Receptacle Assembly: Right Angle, 1.27mm

TE Part # CAT-020-DRAVAP127
D-Sub Receptacle Assembly: Vertical, Action Pin, 1.27mm

TE Part # CAT-AM7-436507
IDC D-Sub: Receptacle Assembly, Panel Mount, Signal, 1.27 mm

TE Part # 5749195-2
68 50SR KIT,ST,UK

TE Part # 5786152-3
68 50SR BKSHL KIT W/JS,UNPNTD,

TE Part # 5749204-2
68 50SR KIT,75D,UK

TE Part # 749195-2
68 50SR KIT,ST,UK

TE Part # CAT-AM7-2250
IDC D-Sub: Plug Assembly, Signal, 1.27 mm

Also in the Series | **AMPLIMITE 0.50 Series**

D-Sub Backshells & Clamps(31)

D-Sub Covers(20)

D-Sub Locking & Mounting(8)

IDC D-Sub Connectors(77)

Insertion & Extraction Tools(1)

PCB D-Sub Connectors(196)

Customers Also Bought



TE Part #1-5750913-7
IDC D-Sub: Connector Kit, Plug, Signal, 1.27 mm

TE Part #1-749656-2
IDC D-Sub: Receptacle Assembly, Panel Mount, Signal, 1.27 mm

TE Part #205161-1
AMPLIMITE,ASY,RCPT,STD,109,1

TE Part #201328-1
CONTACT SOCKET ASSY.

TE Part #204503-1
AMPLIMITE,ASY,PLUG,STD,90,2

TE Part #205164-1
AMPLIMITE,ASY,PLUG,STD,109,2

TE Part #169481-2
HTV10 HAND TOOL, TANDEM SPRING

TE Part #211883-5
SCREW RETAINER KIT,AMPLIMITE

TE Part #163665-000
S02-07-R

TE Part #NB14474001
VERSAFIT-3/8-0-FSP

Documents

Product Drawings
68 50SR CABLE CONN KIT
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5750913-7_O.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_5750913-7_O.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_5750913-7_O.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



AMPLIMITE Subminiature D Connectors - .050 Series Connector

English

AMPLIMITE .050 Series D-sub Connectors QRG

English

Product Specifications

Application Specification

English

Instruction Sheets

Customer Manual (U.S.)

English