

HDP26-24-23SE-L024

✓ ACTIVE

DEUTSCH | DEUTSCH HD, DEUTSCH HDP

TE Internal #: YHDP26-24-23SEL024

Hybrid, Housing for Female Terminals, Wire-to-Wire, 23 Position, Sealable, Black, Wire & Cable, 13A Contact Current Rating (Max), Power & Signal

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Housings > DEUTSCH HDP20 HOUSINGS



Connector & Housing Type: **Housing for Female Terminals**

Mating Pin Diameter: **1.59 mm [.063 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **23**

Sealable: **Yes**

[All DEUTSCH HDP20 HOUSINGS \(282\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	Contact Retainer
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Blank Cavity Position	0
Number of Positions	23

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 48 V



Body Features

Cable Exit Angle	180°
Body Material	PA GF
Primary Product Color	Black

Contact Features

Mating Pin Diameter	1.59 mm[.063 in]
Contact Current Rating (Max)	13 A

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	Add By Accessory
Mating Alignment Type	Polarized

Dimensions

Product Width	49.53 mm[1.95 in]
Product Length	38.3 mm[1.508 in]
Product Height	49.53 mm[1.95 in]
Accepts Wire Insulation Diameter Range	1.35 – 3.05 mm[.053 – .12 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	20mm Flame Test per Standard UL-94

Packaging Features

Packaging Quantity	1
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D48-ST273
DEUTSCH SOLID CONTACTS



TE Part # CAT-D48-SFT273
DEUTSCH STAMPED & FORMED CONTACTS



TE Part # CAT-H396-CH8172
DEUTSCH HDP20 HOUSINGS



TE Part # CAT-D48-SP729
DEUTSCH SEALING PLUGS



TE Part # CAT-H396-B128
DEUTSCH HDP20 BACKSHELLS



TE Part # HD30-24BT-BK
BOOT, 24SZ, ST, BLK



TE Part # HD30-24BT
BOOT, 24SZ, ST, GRY



TE Part # HD30-24BT-90-BK
BOOT, 24SZ, RA, BLK



TE Part # CAT-H3930-B128
DEUTSCH HD30 BACKSHELLS

TE Part # 0411-336-1605
EXT TOOL, SIZE 16, 16-20 AWG, E, DRK BLU

Also in the Series

DEUTSCH HD

Automotive Connector Caps & Covers
(47)

Automotive Housings(670)

Automotive Seals & Cavity Plugs(10)

Insertion & Extraction Tools(11)

Other Automotive Connector
Accessories(11)

Also in the Series

DEUTSCH HDP

Automotive Connector Caps & Covers
(12)

Automotive Housings(289)

Insertion & Extraction Tools(11)

Other Automotive Connector
Accessories(5)

Customers Also Bought





TE Part #YHDP26-24-9SE-L024
DEUTSCH HDP20 HOUSINGS



TE Part #W12P-P004
DEUTSCH DT WEDGELOCKS



TE Part #1-282809-4
TERMI-BLOK PLUG STACKING 4P



TE Part #1-1414687-0
V23136A0004X059-EV-CBOX



TE Part #1-1633711-8
ANVIL, COMB



TE Part #1333227-6
ANVIL, SPECIAL (WIRE/B ONLY)



TE Part #3-1904131-6
V23134A4064X550-EV-CBOX



TE Part #7-2836600-7
OCEAN_2.0_SPARE_PART_KIT-140F2000



TE Part #CZ8952-000
HRHF-250FR-4/97/NM



TE Part #3137796007
RT-375-1-X-30MM

Documents

Product Drawings
PLG, 23P, BLK, E, WTHD, 16, S
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_YHDP26-24-23SEL024_B.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_YHDP26-24-23SEL024_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_YHDP26-24-23SEL024_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English