

5750752-2 ✓ ACTIVE

AMPLIMITE | AMPLIMITE 0.50 Series


TE Internal #: 5750752-2

AMPLIMITE 0.50 Series, D-Sub Backshells & Clamps, Backshell Kit, 68 Position, Shielded, Cable Insulation Diameter Range 13.97 mm [.55 in]

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Backshell Kit**

Number of Positions: **68**

Shielded: **Yes**

Cable Insulation Diameter Range: **13.97 mm [.55 in]**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Backshell Kit
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	68
---------------------	----

Body Features

Boot Material	PVC
Staple Material	Carbon Steel
Color	Black
Staple Plating Material	Tin over Nickel
Backshell Material	Zinc

Mechanical Attachment

Screw & Hole Thread Size	4-40
--------------------------	------



Dimensions

Cable Insulation Diameter Range	13.97 mm [.55 in]
---------------------------------	-------------------

Operation/Application

Shielded	Yes
----------	-----

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Other

Comment	Each enclosure kit contains two backshells, one boot, two jackscrews, one staple and four screws. All are packaged unassembled., Meets SCSI-3 standards
---------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 5749195-2
68 50SR KIT,ST,UK



TE Part # 786531-1
68 DUST COVER, .025 C/L


Also in the Series | AMPLIMITE 0.50 Series



D-Sub Backshells & Clamps(31)




D-Sub Covers(20)



D-Sub Locking & Mounting(8)



IDC D-Sub Connectors(77)



Insertion & Extraction Tools(1)



PCB D-Sub Connectors(196)

Customers Also Bought




TE Part #1-5499923-0
AMP-LATCH UNIVERSAL HEADERS



TE Part #1-5750913-7
IDC D-Sub: Connector Kit, Plug, Signal, 1.27 mm



TE Part #1-350766-2
03P UMNL V0 PLUG HSG RED



TE Part #794001-2
MR RECPT AU PHBZ LP 26-24



Documents

Product Drawings

[68 50SR BSHLL KIT W/BOOT BULK](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_5750752-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_5750752-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5750752-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - .050 Series Connector](#)

English

[AMPLIMITE .050 Series D-sub Connectors QRG](#)

English