



STEP-Z

TE Internal #: 6-1761614-2

PCB Mount Header, Vertical, Board-to-Board, 200 Position, 1.3mm [.051in] Centerline, Partially Shrouded, Gold, Printed Circuit Board

[View on TE.com >](#)

Connectors > PCB Connectors > Board-to-Board Connectors > Board-to-Board Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **200**

Centerline (Pitch): **1.3 mm [.051 in]**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Partially Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Rows	18
Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	200
Board-to-Board Configuration	Parallel

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	500 VAC
Insulation Resistance	18 MΩ
Operating Voltage	48 VAC

Contact Features

Contact Layout	Matrix
Mating Tab Width	1 mm[.04 in]
Mating Tab Thickness	.2 mm[.008 in]



Contact Shape & Form	Dual Beam, Single Beam, Square
PCB Contact Termination Area Plating Material	Tin-Silver
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.76 µm[29.9212 µin]
Contact Type	Tab
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Printed Circuit Board	Surface Mount - Solder Ball
---	-----------------------------

Mechanical Attachment

Mating Retention	With
Mating Alignment	Without
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	1.3 mm[.051 in]
Housing Color	Natural
Housing Material	Thermoplastic

Dimensions

Connector Height	12.95 mm[.509 in]
Row-to-Row Spacing	2 mm[.079 in]
Stack Height	17 mm, 23 mm, 27 mm[1.063 in]
PCB Thickness (Recommended)	1.57 mm[.8 in]

Usage Conditions

Operating Temperature Range	0 – 100 °C[32 – 212 °F]
-----------------------------	-------------------------

Operation/Application

Assembly Process Feature	None
Circuit Application	Power & Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features



Packaging Quantity	25
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-1761615-1
STEP-Z RCPT 11MM 200P LF ST



TE Part # 6-1761615-5
STEP-Z RCPT 15MM 200P LF ST



TE Part # 5-1761615-5
STEP-Z RCPT 05MM 200P LF ST



TE Part # 3-1761615-1
STEP-Z RCPT 05MM 200/104P PB S



TE Part # 3-1761615-3
STEP-Z RCPT 15MM 200/120P PB ST

TE Part # 5-2007615-5
STEP-Z RCPT 05MM 200P LF HT

TE Part # 8-1761615-1
STEP-Z RCPT 05MM 200/104P LF S

TE Part # 8-1761615-2
STEP-Z RCPT 15MM 200/104P LF S

TE Part # 8-1761615-4
STEP-Z RCPT 10MM 200/120P LF S

TE Part # 8-1761615-5
STEP-Z RCPT 15MM 200/112P LF S

Customers Also Bought

TE Part #1-2176050-7
Thick Film Resistor: Current Sense

TE Part #5-1761613-5
STEP-Z RCPT 05MM 104P LF ST

TE Part #2132737-1
IMP100S,R,RA4P6C,LG,39

TE Part #8-2176309-7
RP 1E 0.1W 78R7 0.1% 25PPM 1K RL

TE Part #2170125-1
XFP Cage Assemblies and Kits

TE Part #1658912-5
ASSY, 0.00038MIN AU 3.18 TAIL

TE Part #5-794637-0
20P MICRO MNL ASSY,VRT,SMT LF

TE Part #1546657-2
2P PCV DUAL BARRIER,0.250

TE Part #2-1571990-7
TSPDF11CGVRA004

TE Part #1571586-2
808-AG12D-LF=800 DIP,PCB,SN/SN

Documents



Product Drawings

STEP-Z PLUG 12MM 200P LF ST

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-1761614-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-1761614-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-1761614-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

STEP-Z Interconnection System

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English