



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Receptacle Kit, Panel Mount, Signal, 1.27 mm



Connector & Housing Type: **Receptacle**

Solid Wire Size: **.05 – .1 mm²**

Shielded: **No**

Connector System: **Cable-to-Panel**

[All IDC D-Sub: Receptacle Kit, Panel Mount, Signal, 1.27 mm \(7\)](#)

Features

Product Type Features

Rails	Without
Connector & Housing Type	Receptacle
Connector System	Cable-to-Panel
Connector Product Type	Connector Kit
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	50
Number of Rows	2
Compatible With Wire & Cable Type	Flat Ribbon Cable, Round Jacketed Cable

Body Features

Bracket Material	Zinc
Color	Black
Bracket Plating Material	Nickel over Copper
Cover Material	Polyester
Ribbon Cable Centerline Spacing	.64 mm[.025 in]
Shell Material	Carbon Steel
Shell Plating Material	Nickel over Copper



Contact Features

	30 µin
Contact Mating Area Plating Material	Gold, Gold Flash
Contact Underplating Material	Nickel, Palladium Nickel
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1 A

Termination Features

Termination Cover Type	Standard
Termination Cover Method	Assembled
Termination Cover	With
Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)

Mechanical Attachment

Mating Connector Lock	With
Mounting Angle	None
Mating Connector Lock Type	Latch Blocks
Panel Mount Feature	With
PCB Mount Retention Type	None
Detent	Without
Screw & Hole Thread Size	2-56 UNC
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Polyester
Housing Color	Black
Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Insulation Diameter (Max)	.91 mm
Accepts Wire Insulation Diameter Range	.81 – .91 mm[.032 – .036 in]
Solid Wire Size	.05 – .1 mm²
Wire Size	.05 – .09 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------



Operation/Application

Shielded	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
Cover Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Kit
Packaging Quantity	10

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series | **AMPLIMITE 0.50 Series**

D-Sub Backshells & Clamps(31)	D-Sub Covers(20)	D-Sub Locking & Mounting(8)	IDC D-Sub Connectors(77)
Insertion & Extraction Tools(1)	PCB D-Sub Connectors(196)		

Customers Also Bought

TE Part #6609985-4 CORCOM EJM SERIES IEC FILTERED INLETS	TE Part #324452 AMPOWER PARALLEL SPLICE	TE Part #807117-000 Low Profile Heat Shrink Boots: Poly Molded, Lipped, Straight	TE Part #5-786862-5 IDC D-Sub: Receptacle Kit, Panel Mount, Signal, 1.27 mm
TE Part #YDTS26Z17-35AAV001 D38999: Straight Plug, 17-35 Insert	TE Part #CC1305-000 381A301-780-0	TE Part #CC1306-000 381A302-780-0	TE Part #2993273001 99M1131-18-2/6/9-0
TE Part #8315433001 99M1131-20-2/6/9-0	TE Part #425653-000 RTD-50-P-00		



Documents

Product Drawings

50 50SR PANEL MOUNT RCPT S/A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_786862-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_786862-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_786862-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English