



Connectors > PCB Connectors > Board-to-Board Connectors > Board-to-Board Connector Housings



Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Wire**
Number of Positions: 7
Centerline (Pitch): **2.54 mm [.1 in]**
Number of Rows: 1

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Sealable	No

Configuration Features

Number of Positions	7
Number of Rows	1

Contact Features

Contact Type	Socket
--------------	--------

Housing Features

Housing Color	Black
Centerline (Pitch)	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 215141-3 TANDEM SPR. MT RECPT	TE Part # 215141-5 TANDEM SPR. MT RECPT
---	---

Customers Also Bought



 TE Part #205203-8 D-Sub Crimp Recept Signal 9 Posn, Socket Size 20, Shell Size 1	 TE Part #207020-1 METRIMATE RCPT 36 POS	 TE Part #207018-1 METRIC RCPT 12 POS	 TE Part #205090-1 HD 20 SOCKET CONTACT
 TE Part #207604-1 METRIMATE,STR REL KIT,36P	 TE Part #207601-1 METRIMATE,STR REL KIT,9P	 TE Part #A18003-000 HX-SCE LOW FIRE HAZARD SLEEVES	 TE Part #1-87224-6 16 MODII HDR SRST UNSHRD .100
 TE Part #148423-5 EURO TYPE M REC 42+6,THIN STK	 TE Part #163087-2 062 SOC.ASS.TYP3+		

Documents

Product Drawings

7P MT TAND BU GEH

German

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_928037-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_928037-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_928037-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

English

Product Specification

Japanese

AMP MINI CCOMMON TERMINATION (CT), CONNECTOR, 1.5mm PITCH, M/T TYPE, LEAD FREE VERSION

Japanese

Product Environmental Compliance

TE Material Declaration

English