



EMI Filters > Multi-Function Inlet Filters > CORCOM M SERIES MULTI-FUNCTION INLET FIL



Filter Type: **Power Entry Module**

Input Voltage Selection: **Single AC**

Filter Switch Type: **None**

Filter Shield Type: **Filter Shield**

Mount Angle: **Vertical**

[All CORCOM M SERIES MULTI-FUNCTION INLET FIL \(28\)](#)

Features

Product Type Features

Ground Choke Option	No
Ground Option	None
Filter Type	Power Entry Module
Filter Switch Type	None
Filter Input Termination Type	IEC
Filter Output Termination Type	.110" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Configuration Features

Fuse Options	Dual, Single
--------------	--------------

Electrical Characteristics

Input Voltage Selection	Single AC
Leakage Current (Max) (120VAC, 60Hz)	250 μ A
Leakage Current (Max) (250VAC, 50Hz)	500 μ A
Filter Current Rating	5 A
Voltage Rating (Max)	120 VAC, 240 VAC

Body Features

--	--

Filter Shield Type	Filter Shield
--------------------	---------------

Mechanical Attachment

Mount Angle	Vertical
Filter Mount Style	Flanged

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Other

Comment	Voltage Fixed
---------	---------------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1609142-1
GA400 POWER LINE CO=F6946



TE Part # CAT-C8114-M1
CORCOM M SERIES MULTI-FUNCTION INLET FIL

Also in the Series | Corcom M



Filter Accessories(2)



Multi-Function Inlet Filters(28)



Potentiometers(5)

Customers Also Bought



TE Part #188834-1
Hard Metric Male Connector:
Traditional Backplane, Mezzanine,
2mm



TE Part #206504-4
PLUG ASSY,78 POSN,AMPLIMITE



TE Part #1393117-8
KUP-1D55-24=KU



TE Part #2-6609129-3
CORCOM M SERIES MULTI-FUNCTION INLET FIL




TE Part #205204-9
D-Sub Crimp: Plug, Signal, 9 Posn, Pin
Size 20, Shell Size 1



TE Part #YDTS26W19-11PNV001
D38999: Straight Plug, 19-11 Insert



TE Part #2-1393237-8
RT424012F



TE Part #2-520409-2
ULTRA-FAST 187 ASY REC 22-18 TPBR



TE Part #1-170823-3
187 FASTON SLEEVE,REC.,
TRANSPARENT,NAT



TE Part #1734101-4
Champ050 series,40pos,Au over PdNi



Documents

Product Drawings

5EFM1=F8092

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-6609129-1_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-6609129-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-6609129-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE

English

1654001_CORCOM_PRODUCT_GUIDE_M_SERIES

English

Corcom Combined Selector Charts

English