




Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Terminal & Splice Type: **Ferrule**

Crimp Wire Pin, Tab & Ferrule Terminal Type: **Ferrule**

Crimp Wire Pin, Tab & Ferrule Wire Insulation Diameter (Max): **3.2 mm [.13 in]**

Accepts Wire Insulation Diameter Range: **3.2 mm [.13 in]**

Heavy Duty: **No**

Features

Product Type Features

Crimp Wire Pin, Tab & Ferrule Barrel Type	Closed Barrel
Crimp Wire Pin, Tab & Ferrule Wire/Cable Type	Regular Wire
Sealable	No
Insulated	Yes

Body Features

Sleeve Material	PP/E-Cu
Double Wire	No
Crimp Wire Pin, Tab & Ferrule Plating Material	Tin

Contact Features

Terminal & Splice Type	Ferrule
Crimp Wire Pin, Tab & Ferrule Terminal Type	Ferrule
Crimp Wire Pin, Tab & Ferrule Terminal Orientation	Straight

Termination Features

Bullet Terminal	Without
-----------------	---------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Strip Length	10 mm[.394 in]
Crimp Wire Pin, Tab & Ferrule Wire Insulation Diameter (Max)	3.2 mm[.13 in]



Accepts Wire Insulation Diameter Range	3.2 mm[.13 in]
Wire Size	2583 – 3257 CMA
Barrel Inside Diameter	3.4 mm[.13 in]
Crimp Wire Pin, Tab & Ferrule Material Thickness	.15 mm[.006 in]
Crimp Wire Pin, Tab & Ferrule Overall Length	14.5 mm[.571 in]

Usage Conditions

Insulation Requirement	Fully Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Packaging Features

Packaging Quantity	1000
Crimp Wire Pin, Tab & Ferrule Packaging Method	Strip

Other

Barrel Color	Black
--------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 680314-3
HDM 9SAPR090D G

Customers Also Bought

TE Part #1623731-1
Wirewound Resistor: Vertical Mount

TE Part #1623292-1
CRG0805 1% 8K2

TE Part #130521
PIDG SPADE, 22-16 #4

TE Part #1-1658622-3
44 NOVO MIL/CTR 30DP, LEAD FREE

TE Part #1-1625886-3
1W SM M/OX 5% 3K9

TE Part #1241002-1
ADERENDH1,0M ROT

TE Part #130679
PIDG RING NYL

TE Part #1241000-1
ADERENDHUEL,WS0,5M

TE Part #1241001-1
ADERENDH0,75M GRAU

TE Part #NB15932001
RT-375-1/16-X-STK

Documents

Product Drawings
ADERENDH1,5M SCHWA
English



CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1241003-1_A2.2d_dxf.zip

English

Customer View Model

ENG_CVM_1241003-1_A2.3d_igs.zip

English

Customer View Model

ENG_CVM_1241003-1_A2.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

Wire Ferrules

English

WIRE END FERRULES

English