




PIDG

TE Internal #: 131330
PIDG, Crimp Wire Pins, Tabs & Ferrules, Tab, Tab, Crimp Wire Pin,
Tab & Ferrule Tab Width .115 in [2.92 mm], Tab Thickness .79 mm [.031 in]
[View on TE.com >](#)

Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules > PIDG TABS



Terminal & Splice Type: **Tab**
Crimp Wire Pin, Tab & Ferrule Terminal Type: **Tab**
Crimp Wire Pin, Tab & Ferrule Tab Width: **2.92 mm [.115 in]**
Tab Thickness: **.79 mm [.031 in]**
Crimp Wire Pin, Tab & Ferrule Wire Insulation Diameter (Max): **4.32 mm [.17 in]**

[All PIDG TABS \(8\)](#)

Features

Product Type Features

Shape Description	WIRE PIN-004
Crimp Wire Pin, Tab & Ferrule Barrel Type	Closed Barrel
Crimp Wire Pin, Tab & Ferrule Wire/Cable Type	Regular Wire
Sealable	No
Insulated	Yes
Support Style	Insulation Support

Body Features

Sleeve Material	Nylon
Insulation Sleeve Material	Nylon
Double Wire	No
Crimp Wire Pin, Tab & Ferrule Plating Material	Tin

Contact Features

--	--



Terminal Length	10 mm, 9 mm[.43 in]
Terminal & Splice Type	Tab
Crimp Wire Pin, Tab & Ferrule Terminal Type	Tab
Tab Thickness	.79 mm[.031 in]
Crimp Wire Pin, Tab & Ferrule Terminal Orientation	Straight

Termination Features

Bullet Terminal	Without
-----------------	---------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

DIN Wire Size	1 – 2.5 mm ²
Crimp Wire Pin, Tab & Ferrule Tab Width	2.92 mm[.115 in]
Crimp Wire Pin, Tab & Ferrule Wire Insulation Diameter (Max)	4.32 mm[.17 in]
Accepts Wire Insulation Diameter Range	4.32 mm[.17 in]
Wire Size	2050 – 5180 CMA
Barrel Inside Diameter	4.4 mm[.173 in]
Crimp Wire Pin, Tab & Ferrule Material Thickness	.79 mm[.031 in]
Crimp Wire Pin, Tab & Ferrule Overall Length	22.63 mm[.891 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Packaging Features

Packaging Quantity	1000
Crimp Wire Pin, Tab & Ferrule Packaging Method	Loose Piece

Other

Barrel Color	Blue
--------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 58433-3 PRO CR ASSY, RBY IS9252	 TE Part # 59250 T-HEAD PIDG 26-14 ASSY	 TE Part # 47387 DAHT PG PIDG 20-14 ASSY	 TE Part # 58423-1 DIE, RBY IS9252
 TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	 TE Part # 539691-2 ERGO DIE R.B.Y	 TE Part # 2063030-1 SDE DIESET, RBY, UL	 TE Part # 47807-1 DIES PIDG 16-14 DIE SET



TE Part # 169404
CERTI-LOK DIE

TE Part # 169400
CERTI-LOK

Also in the Series | PIDG

Compression Connectors(17)

Crimp Terminal Housings(1)

Crimp Wire Pins, Tabs & Ferrules(41)

Knife Disconnects(11)

PCB Terminals(9)

Portable Crimp Tools(2)

Quick Disconnects(53)

Ring Terminals & Spade Terminals(862)

Special Purpose Terminals(1)

Splices(48)


Customers Also Bought

TE Part #165046
PIDG FORMED WIRE PINS

TE Part #130516
PIDG SPADE

TE Part #150730
22-16 PIDG TAB 3,3/3

TE Part #130008
PIDG RING TONGUE TERMINALS



Documents

Product Drawings

PIDG, WIRE, TAB, 16-14

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_131330_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_131330_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_131330_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PIDG TERMINALS & SPLICES Quick Reference Guide

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English