




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **9**

Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Columns	3
Number of Loaded Positions	9
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	9
Number of Rows	3

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Layout	Matrix
PCB Contact Termination Area Plating Material Thickness	3.81 μm[150 μin]
Mating Pin Diameter	1.75 mm[.069 in]



Contact Underplating Material Thickness	2.54 µm[100 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Underplating Material	Copper
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	3.81 µm[150 µin]
Contact Type	Pin
Contact Current Rating (Max)	7.5 A

Termination Features

Round Termination Post & Tail Diameter	.99 mm[.039 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention Type	Screw Mount
PCB Mount Alignment	Without
Mating Retention	With
PCB Mount Retention	With
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	5 mm[.197 in]
Housing Color	Black
Housing Material	PA 66

Dimensions

Connector Length	17.78 mm[.7 in]
Connector Height	11.79 mm[.464 in]
Connector Width	18.72 mm[.737 in]
Row-to-Row Spacing	5 mm[.197 in]

Usage Conditions

Operating Temperature Range	-55 – 130 °C[-67 – 266 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

--	--



UL Flammability Rating	UL 94V-0
Agency/Standard	CSA, UL
UL Rating	Recognized
VDE Tested	Yes

Packaging Features

Packaging Quantity	70
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 207439-1
9 POS SQ GRID METRIMATE-PLUG

Also in the Series | AMP Metrimate



Insertion & Extraction Tools(1)



Rectangular Boots & Strain Relief(9)



Rectangular Connector Hardware(4)



Rectangular Connector Housings(35)



Rectangular Connector Keying Plugs(1)



Rectangular Contact Inserts(7)



Rectangular Power Connectors(2)



Standard Rectangular Connectors(5)



Wire-to-Board Headers & Receptacles
(83)

Customers Also Bought




TE Part #2-917809-2
DYNAMIC 5000 REC AND TAB HSG



TE Part #826469-3
2X3P MOD II SHROUDED HEADER, ST



TE Part #1676697-1
RN 0805 43R2 0.1% 10PPM CUT LENGTH



TE Part #1879747-1
RP 1J 63K4 0.1% 15PPM CUT LENGTH



TE Part #1478763-9
METAL BACKSHELL 9 WAY 45 DE

TE Part #1-206763-1
METRIMATE PIN HEADER ASSY,24P

TE Part #2-1445052-4
MICRO MNL HDR ASSY S/ROW LF

TE Part #2-2232263-1
PTL 1X2 CAP PANEL MT HOT WIRE KEY B NAT

TE Part #2-1571550-4
DIP Socket: Standard, Screw Machine, Closed, Gold

TE Part #1423254-6
P40C42A12C1-120=CONTACTOR ASSEMBLY

Documents

Product Drawings

METRIMATE PIN HEADER ASSY,9P

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_207441-7_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_207441-7_M.3d_igs.zip

English

Customer View Model

ENG_CVM_207441-7_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

METRIMATE_PIN_SOCKET_CATALOG

English

Product Specifications

Product Specification

English

Product Environmental Compliance

MD_207441-7_052920181157_dmtec



English

[MD_207441-7_052920181157_dmtec](#)

English

[Agency Approvals](#)

[CSA Certificate](#)

English