




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **1.65 – 5.26 mm²**

Quick Disconnect Mating Tab Width: **6.35 mm [.25 in]**

Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Low
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Pre-Tin

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle



Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
Extraction Force	7 – 100 Newton
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	3.81 – 5.08 mm[.15 – .2 in]
Overall Length	25.8 mm[1.016 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Wire Size	1.65 – 5.26 mm²
Quick Disconnect Mating Tab Width	6.35 mm[.25 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Rating	Recognized
-----------	------------

Packaging Features

Packaging Quantity	3000
Quick Disconnect Packaging Method	Strip/Reel

Other

Comment	Air-feed Applicator should be used.
---------	-------------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2021
(211)
Candidate List Declared Against: JAN 2021
(211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 172076-6 POSITIVE LOCK 250 HOUSING RECEPTACLE	TE Part # 172076-1 POSITIVE LOCK 250 HOUSING RECEPTACLE	TE Part # 2-172076-1 250 HSG. PL MKII REC. NAT	TE Part # 1969864-1 2P, 250 SERIES, POSITIVE LOCK MARK II
TE Part # 2-521229-1 PL EXII & FASTON 250 HSG 2P NAT	TE Part # 724659-2 EXT TOOL FOR POSITIVE .250	TE Part # 2-172076-6 PL 250 REC HSG 1P NYLON BLUE	TE Part # 2-172076-7 POSITIVE LOCK 250 HOUSING RECEPTACLE





 TE Part # 172076-2 PL MKII 250 REC HSG 1P NYLON BLACK	 TE Part # 341299-2 PL 250 REC TERMINAL 20-15 AWG PTPB	 TE Part # 2-172076-2 POSITIVE LOCK 250 HOUSING RECEPTACLE	 TE Part # 178833-1 POSITIVE LOCK .250 HOUSING RECEPTACLE
 TE Part # 521229-1 PL 250 HOUSING RECEPTACLE NYLON 6/6	 TE Part # 177627-1 PL .250 (6.3 MM) HOUSING RECEPTACLE	 TE Part # 172076-7 PL MKII 250 REC HSG 1P NYLON RED	 TE Part # 174429-1 PL 250 HOUSING RECEPTACLE
 TE Part # 177627-7 PL .250 (6.3 MM) HOUSING RECEPTACLE	 TE Part # 1969820-1 250 HIGH TEMP POS LOCK HSG LCP	 TE Part # 172076-4 POSITIVE LOCK 250 HOUSING RECEPTACLE	 TE Part # 172076-5 POSITIVE LOCK 250 HOUSING RECEPTACLE

Also in the Series | Positive Lock 250

 Automotive Terminals(1)	 Crimp Terminal Housings(203)	 Insertion & Extraction Tools(3)	 Insulation Boots & Sleeves(6)
 Quick Disconnects(189)			

Customers Also Bought



 TE Part #1-1376389-2 STD Temp Power Key Plug	 TE Part #1376394-1 Power Key TPA	 TE Part #917689-1 STD Temp Signal Double Lock Plug	 TE Part #1-179472-6 CT DBL ROW HOLDER, CRIMP, 16P, NA
 TE Part #1-174712-1 187 HSG. PL MKII REC. 6.65mm 2P NAT	 TE Part #1318954-1 250 HSG. PL EX REC. NAT	 TE Part #1217039-1 TIMER CONNECTOR GEN 3 18-14 POST-TPBR	 TE Part #1-172127-1 FF 250 REC HSG 1P NYLON NAT

Documents

Product Drawings

250 PL MKII REC. 15-10AWG PTBR

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170329-1_W1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170329-1_W1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170329-1_W1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Positive Lock Receptacles

English

POS_LOCK_MII_QRG

English

Product Specifications

Application Specification

English



Product Environmental Compliance

[MD_170329-1_053120181024_dmtec](#)

English

[MD_170329-1_053120181024_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[AMP* POSITIVE LOCK CONNECTOR](#)

English

Agency Approvals

[Agency Approval Document](#)

English