



Connectors > Lighting Connectors > Poke-In Connectors



Connector System: **Wire-to-Board**
Number of Positions: 1
Centerline (Pitch): **.16 mm [4 in]**
Sealable: **No**
Connector & Contact Terminates To: **Printed Circuit Board**

Features

Product Type Features

Connector Type	Connector Assembly
Connector Style	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	1
---------------------	---

Contact Features

Contact Current Rating (Max)	6 A
------------------------------	-----

Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---------------------------------------------	---------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	.16 mm[4 in]
--------------------	--------------

Dimensions

Connector Height	.23 mm[5.8 in]
------------------	----------------



Wire Size

24 – 22 AWG

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-2106431-1
Connector, SMT-IDC PASS THRU, 1 POS, 24



TE Part # 7-2106003-1
Connector, SMT-IDC,1 pos, 24AWG, black


Also in the Series | Insulation Displacement Connectors Closed End



Ballast Connectors(23)



Poke-In Connectors(66)



Wire-to-Board Headers & Receptacles (1)

Customers Also Bought



TE Part #1-2308340-8
D-SUB BACKSHELL SIZE 1



TE Part #1-2106003-2
Connector, SMT-IDC, 2 POS, 20 AWG



TE Part #1445048-3
PANEL MT SINGL ROW HSG 3 POS




TE Part #1445049-6
FREE HANG SINGL ROW HSG 6 POS



TE Part #1879208-7
CPF 0402 18R 0.1% 25PPM 1K RL



TE Part #1623168-1
CRG0805 1% 270K



TE Part #1-1888291-1
FPH-0921G=FLXPAC HDR P 09 ST LF



TE Part #1-794615-6
PANEL MT DBL ROW HSG 16 POS



TE Part #1-794616-6
FREE HANG DBL ROW HSG 16 POS



TE Part #ZPF00000000019494
FDPA 56-20-16 PN-K 059



Documents

Product Drawings

Connector, SMT-IDC, 1 POS, 24 AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-2106003-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-2106003-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-2106003-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

IDC_SSL_CONNECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English