



Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**

Operating Voltage: **250 VDC**

Contact Mating Area Plating Material: **Pre-Tin**

Wire Size: **20 – 14 AWG**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Contact Features

Contact Mating Area Plating Material	Pre-Tin
Contact Current Rating (Max)	10 A
Contact Type	Socket
Contact Retention Within Housing	With
Mating Pin Diameter	2.1 mm[.082 in]
Contact Base Material	Phosphor Bronze
Wire Contact Termination Area Plating Material Thickness	.4 µm[15.74 µin]
Wire Contact Termination Area Plating Material	Pre-Tin
Wire Contact Termination Area Plating Material Finish	Bright



Contact Orientation	Straight
---------------------	----------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Connector Mounting Type	Cable Mount (Free-Hanging)
Wire Insulation Support	Without

Dimensions

Wire Size	.52 – 2.27 mm ²
Accepts Wire Insulation Diameter Range	3.3 mm[.13 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
VDE Tested	No

Packaging Features

Packaging Method	Reel
Packaging Quantity	5000

Other

Wire/Cable Type	Discrete Wire
Wire Type	Stranded
For Use With	Commercial MATE-N-LOK housings

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JAN 2021
(211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-171196-0
6 POS MATE-N-LOK S

TE Part # 1-480274-0
09P CMNL PLUG HSG P/M NATL

TE Part # 1-480284-0
08P CMNL CAP HSG M/M NATL

TE Part # 1-480438-0
16P CMNL PLUG HSG M/M NATL

TE Part # 1-480683-0
02P CMNL PLUG HSG F/H NATL

TE Part # 1-480277-0
09P CMNL CAP HSG P/M NATL






TE Part # 1-480304-0
03P CMNL PLUG HSG P/M NATL

TE Part # 1-480722-0
04P CMNL PLUG HSG W/LCK NATL



 TE Part # 1-480276-0 06P CMNL CAP HSG P/M NATL	 TE Part # 1-480285-0 10P CMNL PLUG HSG M/M NATL	 TE Part # 1-480439-0 16P CMNL CAP HSG M/M NATL	 TE Part # 1-480393-1 02P CMNL PLUG HSG F/H BLK
 TE Part # 1-480345-0 08P CMNL CAP HSG F/H NATL	 TE Part # 1-480340-0 06P CMNL CAP HSG F/H NATL	 TE Part # 1-480278-0 12P CMNL CAP HSG P/M NATL	 TE Part # 1-480425-0 04P CMNL PLUG HSG P/M NATL
 TE Part # 1-480324-0 15P CMNL CAP HSG P/M NATL	 TE Part # 1-480721-0 03P CMNL PLUG HSG W/LOK NATL	 TE Part # 1-480323-0 15P CMNL PLUG HSG P/M NATL	 TE Part # 170924-1 MNL 2 POS NATURAL PIN HSG

Also in the Series | Commercial MATE-N-LOK

 Connector Contacts(26)	 Crimp Wire Pins, Tabs & Ferrules(3)	 Insertion & Extraction Tools(5)	 Power Contacts(129)
 Rectangular Caps & Covers(2)	 Rectangular Connector Housings(17)	 Rectangular Connector Seals(1)	 Rectangular Power Connectors(171)



Standard Circular Connectors(4)



Standard Rectangular Connectors(10)



Wire-to-Board Connector Contacts(1)


Customers Also Bought



TE Part #170120-1
MATE-N-LOK SOCKET 2




TE Part #1473809-1
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part #170020-2
SHUR PLUG 20-14 MM2 TPBR



TE Part #1-174360-1
E-J MK-2 CAP HSG 3P NATURAL



TE Part #1-174355-1
E-J MK-2 CAP HSG 2P NATURAL




TE Part #170092-2
FF 250 REC 18-14AWG TPPB
REREELING



TE Part #1-1318382-9
025 16POS CAP ASSY H RND



TE Part #1417970001
SAS-115-075-1017-1X



TE Part #1473867-1
040 MLC 8POS CAP OUTER HSG



TE Part #918254-1
INS,CRIMPER

Documents

Product Drawings
MATE-N-LOK SOCKET

English

CAD Files
3D PDF

English

Customer View Model
ENG_CVM_170120-4_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_170120-4_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_170120-4_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Agency Approvals

[Agency Approval Document](#)

English