




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **.51 – 1.31 mm²**

Quick Disconnect Mating Tab Width: **4.75 mm [.187 in]**

Quick Disconnect Mating Tab Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Tin

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle



Quick Disconnect Terminal Orientation	Flag
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
Extraction Force	14.7 Newton
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.79 – 4.32 mm [.11 – .17 in]
Overall Length	13.5 mm [.531 in]
Receptacle Terminal Stock Thickness	.3 mm [.012 in]
Wire Size	.51 – 1.31 mm ²
Quick Disconnect Mating Tab Width	4.75 mm [.187 in]
Quick Disconnect Mating Tab Thickness	.51 mm [.02 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Industry Standards

UL Rating	Listed
-----------	--------

Packaging Features

Packaging Quantity	1000
Quick Disconnect Packaging Method	Loose Piece/Carton

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2021 (211)
Candidate List Declared Against: JAN 2021 (211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 170203-2 187 FASTON,REC.,24-20 AWG,TPBR	 TE Part # 61045-2 FASTON .187 SERIES (4.8 MM) TPBR	 TE Part # 170466-1 187 FASTON,REC.,18-14 AWG,TPBR	 TE Part # 5-160491-1 FASTON 187 REC 1.0-2.5 MM2 PLAIN BR
 TE Part # 151791-1 FLAG FASTON RECEPTACLE	 TE Part # 42566-1 FASTON 187 RECEPTACLE 20-16 AWG BR	 TE Part # 42566-2 FASTON 187 RECEPTACLE 20-16 AWG TPBR	 TE Part # 5-160491-2 FASTON 187 13 1.0-2.5MM TPBR




TE Part # 151791-2
FASTON 375 REC FLAG 12-10 AWG
TPBR LP



TE Part # 170123-2
205 FASTON,REC.,22-18 AWG,TPBR




TE Part # 180439-2
110 FASTON,REC.,20-16 AWG,TPBR



TE Part # 5-160493-2
FASTON 187 RECEPTACLE 0.5-1.5
MM2 TPBR

Also in the Series | FASTON 187



Crimp Terminal Housings(40)



Insertion & Extraction Tools(1)



Joints & Splices(1)



PCB Terminals(48)




Quick Disconnects(222)




Splices(1)


Customers Also Bought



TE Part #172127-1
FF 250 PLUG HSG 1P NYLON NAT




TE Part #170341-1
FF 250 TAB 14-12AWG BR WITHOUT
LATCH



TE Part #1674558-1
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part #1554369-1
AMPSEAL 16 HOUSINGS




TE Part #171810-2
POSITIVE LOCK HOUSING
RECEPTACLE




TE Part #170003-5
SHUR PLUG .196(5 MM) REC 20-14
MM2 TPBR



TE Part #170823-9
110 FASTON SLEEVE,REC.,
TRANSPARENT,NAT



TE Part #172127-2
FF 250 PLUG HSG 1P NYLON BLACK



Documents

Product Drawings

187 FASTON,FLAG,REC.,20-16 AWG,TPBR

Japanese

187 FASTON,FLAG,REC.,20-16 AWG,TPBR

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170141-2_AB.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170141-2_AB.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170141-2_AB.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

.187 Series Flag FASTON Receptacle

English

Agency Approvals

UL Report

English