




Terminals & Splices > Splices



Splice Product Type: **Splice**

Terminal & Splice Type: **Splice**

Wire Size: **.33 – 6 mm²**

Sealable: **No**

Features

Product Type Features

Splice Product Type	Splice
Sealable	No
Splice Type	In-Line Splice
Serrated	No
Splice Accessory Type	Splice
Insulated	Yes

Configuration Features

Splice Capacity	1
-----------------	---

Body Features

Weight per Piece	1.68 g
Plating Material	Tin
Insulation Material	Vinyl
Splice Material	Brass

Contact Features

Contact Plating Material	Tin
Terminal & Splice Type	Splice

Housing Features

Housing Material	PVC
------------------	-----

Dimensions

--	--



Wire Size	.33 – 6 mm²
Splice Material Thickness	.81 mm[.032 in]
Splice Overall Length	53.16 mm[2.093 in]

Usage Conditions

Insulation Requirement	Fully Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

RU (UL Component Program)	No
CSA Certified	No
Government Qualified Splice	No

Packaging Features

Packaging Quantity	500
Splice Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 184261-1
RCPT,PIDG FASTON 250 LIF 22-18

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(143)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(144)

Quick Disconnects(466)

Splices(4)

Customers Also Bought

TE Part #55830-2
AMPOWER TERMINAL CENTERLINE 2 HOLES

TE Part #321286
PG BUTT 12-10

TE Part #5-643819-0
20P MTA156 CONN ASSY 22AWG LF

TE Part #325610
AMPOWER TERMINAL WO STUD HOLE



TE Part #208063-5
SKT ASSY,36 POSN,METRIMATE

TE Part #208062-8
PIN ASSY,36 P,MMATE LF

TE Part #6-1618071-7
255-6X=WILMAR OVER /UNDervOLTAG

TE Part #2-1618071-3
25-060-7X=WILMAR FREQUENCY 120

TE Part #766667-2
Wave Crimp, Flat to Round 8 AWG Cbl Assy

Documents

Product Drawings

RECEPT, FASTON SPLICE 22-10

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_321688_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_321688_G.3d_igs.zip

English

Customer View Model

ENG_CVM_321688_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

Agency Approval Document

English