



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **7**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Header Type	Unshrouded
Rectangular Power Connector Type	Header
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	7
PCB Mount Orientation	Vertical
Number of Power Positions	7
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Body Features



Connector Profile	Low
-------------------	-----

Contact Features

Contact Layout	Inline
Contact Base Material	Brass
Contact Current Rating (Max)	8 A
Contact Retention Within Housing	Without
Contact Type	Pin, Tab
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	1 µm[39.37 µin]
Contact Termination Area Plating Thickness	.8 µm[31.49 – 70.86 µin]

Termination Features

Termination Post & Tail Length	3.7 mm[.146 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment	With
PCB Mount Alignment	Without
PCB Mount Retention	Without
Connector Mounting Type	Board Mount
Mating Retention	With
Mating Retention Type	Latch

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
Housing Color	Natural
Housing Material	PBT GF

Dimensions

PCB Thickness (Recommended)	.06 mm[1.6 in]
Width	10.7 mm[.421 in]
Mating Post Length	7.7 mm[.3 in]
Height	8.2 mm[.32 in]
Length	27.66 mm[1.089 in]

Usage Conditions



Operating Temperature Range	-25 – 105 °C[-13 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Method	Bag
Packaging Quantity	650

Other

For Use With	Plug Housing
--------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>










EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 TE Part # 1-1123723-9 3.96 EP HDR ASSY 9P(NATURAL)	 TE Part # 1744416-7 7 POS EP II HSG, GLOW WIRE	 TE Part # 1-1123723-4 3.96 EP HDR ASSY 4P(NATURAL)	 TE Part # 1-1123723-8 3.96 EP HDR ASSY 8P(NATURAL)
 TE Part # 1-1318301-4 3.96EP HDR ASSY 4(7)P NAT/TUBE	 TE Part # 1-1123723-0 3.96 EP HDR ASSY 10P(NATURAL)	 TE Part # 1-1123724-4 3.96EP HDR ASSY 4(7)P NATURAL	 TE Part # 1-1123723-1 3.96 EP HDR ASSY 11P(NATURAL)
 TE Part # 1-1123723-7 3.96 EP HDR ASSY 7P(NATURAL)	 TE Part # 1-2316952-0 3.96 EP HDR ASSY 10P, NO PIN 2,4,6,9	 TE Part # 2-1123724-4 3.96EP HDR ASSY 4(7)P YELLOW	 TE Part # 7-1123724-1 3.96EP HDR ASSY 4(7)P (NATURAL GWT)

Also in the Series | Economy Power

 Connector Contacts(1)	 Insertion & Extraction Tools(1)	 PCB Latches, Locks & Retainers(2)	 Power Contacts(5)
 Rectangular Connector Housings(1)	 Rectangular Power Connectors(260)	 Wire-to-Board Connector Assemblies & Housings(41)	 Wire-to-Board Connector Contacts(6)



Wire-to-Board Headers & Receptacles (162)

Customers Also Bought



TE Part #2-1747066-3
GRACE INERTIA CONN 2.5 PLUG
HSG 3P BLUE



TE Part #1217214-1
TAB, POKE-IN, MAG-MATE



TE Part #1-1971030-3
STD Temp Sig GRACE INERTIA Plug




TE Part #1871843-2
GIC 2.5 HDR ASSY TIN VERSION 2P



TE Part #964339-1
MAG MATE KONT. MKII



TE Part #2-1123824-1
EP 1P HDR YELLOW



TE Part #2-172210-1
PL MKII 187 REC HSG 2P NAT



TE Part #2-1971904-4
TPA 8POS,NEW GIC3.3



TE Part #2316952-4
3.96 EP HDR ASSY 4P, NO PIN 2,3



TE Part #2316952-8
3.96 EP HDR ASSY 8P, NO PIN 2,4,6,7

Documents

Product Drawings

3.96 EP HDR ASSY 7P, NO PIN 1,3,5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2316952-7_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2316952-7_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2316952-7_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English