



Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **3.31 – 5.26 mm²**

Quick Disconnect Mating Tab Width: **6.35 mm [.25 in]**

Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Low
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Pre-Tin

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle



Quick Disconnect Terminal Orientation	Flag
Contact Base Material	Brass
Crimp Type	Tab-Lok
Barrel Type	Open

Mechanical Attachment

Extraction Force	7 – 100 Newton
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.8 – 4.9 mm[.11 – .193 in]
Overall Length	20.8 mm[.82 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Wire Size	3.31 – 5.26 mm²
Quick Disconnect Mating Tab Width	6.35 mm[.25 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Rating	Recognized
-----------	------------

Packaging Features

Packaging Quantity	2000
Quick Disconnect Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-176497-1
250 HSG. PL EX FLAG REC. NAT




TE Part # 176497-1
POSITIVE LOCK .250 Hsg (6.3 MM) V2



TE Part # 2232343-1
250 PL EX FLAG REC. 18-12AWG PTBR



TE Part # 1-176497-9
PL EX SLEEVE 250 FLAG BLACK 6/6 NYLON



TE Part # 1-176497-7
PL EX SLEEVE 250 FLAG RED 6/6 NYLON



TE Part # 1-176497-4
250 POSITIVE LOCK REC EX SLEEV



TE Part # 1-176497-6
PL EX 250 REC HSG 1P NYLON BLUE



TE Part # 1855688-1
HDM-FA-EA-HB-LM & BENCH G-CUT



TE Part # 2232343-2
250 PL EX FLAG REC. 18-12AWG PTBR FLAT

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(203)



Insertion & Extraction Tools(3)



Insulation Boots & Sleeves(6)




Quick Disconnects(189)


Customers Also Bought



TE Part #1565079-1
GRACE INERTIA Receptacle



TE Part #170183-2
250 FASTON,REC.,22-18 AWG,TPBR




TE Part #170063-2
CLUSTER PIN REC



TE Part #1565081-1
STD Temp GRACE INERTIA Plug



TE Part #1565088-1
STD Temp GRACE INERTIA Cap



TE Part #908917-1
ANVIL,INSERT




TE Part #1-172132-1
FF 250 PLUG HSG 3P NYLON NAT



TE Part #1-1747066-6
GRACE INERTIA CONN 2.5 PLUG HSG 6P RED



TE Part #1376477-2
2.5MM PITCH SIGNAL MATE CONN



TE Part #1-174880-1
E-J MK-2 CAP HSG 1P NATURAL

Documents



Product Drawings

PL EX 250 REC TERMINAL-FLAG 12-10 PTPB

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_175178-1_L_c-175178-1-l.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_175178-1_L_c-175178-1-l.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_175178-1_L_c-175178-1-l.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_175178-1_053120182151_dmtec

English

MD_175178-1_053120182151_dmtec

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

POSITIVE LOCK EX CONTACT

English