



EMI Filters > Multi-Function Inlet Filters



Filter Type: **Power Line**

Mount Angle: **Right Angle**

Leakage Current (Max) (120VAC, 60Hz): **220 µA**

Leakage Current (Max) (250VAC, 50Hz): **380 µA**

Filter Current Rating: **1 A**

Features

Product Type Features

Ground Choke Option	No
Ground Option	None
Filter Type	Power Line
Filter Input Termination Type	IEC
Filter Output Termination Type	Wire Lead
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	220 µA
Leakage Current (Max) (250VAC, 50Hz)	380 µA
Filter Current Rating	1 A
Voltage Rating (Max)	250 VAC

Mechanical Attachment

Mount Angle	Right Angle
Filter Mount Style	Flanged

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #154N-015G-R
MEDIA ISOLATED PRESSURE STOCK LIST



TE Part #5-1609152-6
CORCOM SRB SERIES IEC FILTERED INLETS



TE Part #2057833-1
SFP+ Enhanced 1x4 Cage Assy




TE Part #2213765-7
AV19 SPM 5A SPOT LED RED 24V



TE Part #YDTS24F15-35SB0000
D38999: Jam Nut, 15-35 Insert, Electroless Nickel Plating



TE Part #1-6609106-4
CORCOM P SERIES MULTI-FUNCTION INLET FIL



TE Part #1051810-1
SMA CABLE PLUG 2031 8125 92



TE Part #2-2301994-3
RJ45 JACK INT.MAG. 1GB LED 1X1



TE Part #2-1624116-6
BMB-A 0603 40R N8



TE Part #1623988-1
SC15-10-1035-10 39UH AMMO 1000

Documents

Product Drawings
1EEJ8=F8007

English

CAD Files
Customer View Model
ENG_CVM_3-6609006-2_0.3d_igs.zip
English
Customer View Model
ENG_CVM_3-6609006-2_0.3d_stp.zip
English
Customer View Model
ENG_CVM_3-6609006-2_0.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE_EEJ_SERIES](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English