




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Cluster Blocks



Cluster Block Product Type: **Terminal Housing**

Number of Circuits: **2**

Cluster Block Material: **PBT GF**

Features

Product Type Features

Cluster Block Product Type	Terminal Housing
Applies To	Wire/Cable
Wire/Cable Type	Magnet Wire

Configuration Features

Number of Circuits	2
Preloaded	No

Body Features

Cluster Block Material	PBT GF
Color	Natural

Contact Features

Pin Diameter	2.29 mm[.09 in]
--------------	-----------------

Mechanical Attachment

Mount Configuration	2 Forward - 1 Back
Polarized	No

Dimensions

Accepts Wire Insulation Diameter Range	1.5 – 2.6 mm[.059 – .103 in]
--	------------------------------



Length

30.5 mm[1.2 in]

Operation/Application

Connects To	Cluster Block Reverse Housing
-------------	-------------------------------

Packaging Features

Packaging Method	Box
Packaging Quantity	5000

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings
CLUSTER BLOCK HSG .090 DIA. RE
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_284406-1_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_284406-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_284406-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

Product Specifications

[Special rec. cluster ctc. f. 090 dia. p/n 284633-1](#)

English

Application Specification

English

Agency Approvals

UL Report

English