

MAG-MATE

TE Internal #: 2232556-1


MAG-MATE, Magnet Wire Terminals, Tab, Tab, Magnet Wire

Terminal Mating Tab Width 6.35 mm [.25 in]

[View on TE.com >](#)



Terminals & Splices > Magnet Wire Terminals



Terminal & Splice Type: **Tab**
Magnet Wire Terminal Terminal Type: **Tab**
Magnet Wire Terminal Mating Tab Width: **6.35 mm [.25 in]**
Magnet Wire Terminal Mating Tab Thickness: **.81 mm [.032 in]**
Terminal Height: **7.05 mm [.278 in]**

Features

Product Type Features

Magnet Wire Terminal Wire/Cable Type	Magnet Wire
Sealable	No

Body Features

Magnet Wire Terminal Plating Material	Tin
---------------------------------------	-----

Contact Features

Terminal & Splice Type	Tab
Magnet Wire Terminal Terminal Type	Tab

Termination Features

Magnet Wire Terminal Termination Method	IDC Standard
---	--------------

Mechanical Attachment

Magnet Wire Terminal Mating Retention Type	Barbs, Dimple
--	---------------

Dimensions

Magnet Wire Terminal Mating Tab Width	6.35 mm[.25 in]
Magnet Wire Terminal Mating Tab Thickness	.81 mm[.032 in]



Terminal Height	7.05 mm[.278 in]
Aluminum Wire Size	1.02 – 1.15 mm
Magnet Wire Size	19 – 17 AWG
Magnet Wire Terminal Material Thickness	.8 mm[.032 in]
Stock Thickness (Magnet Wire Side)	.41 mm[.016 in]
Magnet Wire Terminal Overall Length	21.21 mm[.835 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Packaging Features

Packaging Quantity	3000
Magnet Wire Terminal Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 63614-1 MAG-MATE 250 TAB 19-17 TPBR	 TE Part # 1217031-1 MAG-MATE 250FTAB 22-20 016TPBR	 TE Part # 1217860-1 TAB,250 FASTON, MAG-MATE	 TE Part # 1217924-1 TAB,250 FASTON,MAG-MATE
 TE Part # 2232237-1 MAG-MATE W/250 CONN TAB TPBR	 TE Part # 2232555-1 MAG-MATE W/250 CONN TAB TPBR	 TE Part # 63720-2 TAB,250 MAG-MATE SLIM LN 19-17	 TE Part # 1217870-1 TAB,250 FASTON,MAG-MATE
 TE Part # 1217994-1 TAB,187X032 FASTON,MAG-MATE	 TE Part # 2232683-1 MAG-MATE W/250 CONN TAB TPBR	 TE Part # 63463-1 MAG-MATE W/118 CONN TAB TPBR	 TE Part # 63740-2 TAB,250 MAG-MATE SLIM LN 19-17
 TE Part # 2232237-2 MAG-MATE W/250 CONN TAB TPBR			

Also in the Series | MAG-MATE



Insertion & Extraction Tools(8)



Magnet Wire Terminals(468)



PCB Terminals(1)

Customers Also Bought



TE Part #1721441-2
PCN 3A/5A SLIM PCB RELAY 5VDC



TE Part #2-1623779-3
Wirewound Resistor: Vertical Mount



TE Part #2-1879071-9
Power Resistor: Aluminum Housed, 75 Watt



TE Part #1624094-2
3613C 100UH 10%



TE Part #2134611-1
Micro poke in assembly



TE Part #1624097-3
3615A-10-3549-10 1.0MH




TE Part #5-2154874-3
LED Holder for Cree CXA25XX (1pc)



TE Part #1676979-2
TW 1W 100R 6.35X25PL



TE Part #178303-3
DYNAMIC 3100 HDR ASSY



TE Part #1-2176084-2
EP 7W (S) 680R 5%

Documents

Product Drawings

MAG-MATE W/250 CONN TAB TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2232556-1_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2232556-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2232556-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Magnet Wire Terminals & Splices](#)

English

Product Specifications

[Application Specification](#)

English