




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **.32 – .82 mm²**

Quick Disconnect Mating Tab Width: **2.8 mm, 3.18 mm [.11 in, .125 in]**

Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire/Cable Type	Regular Wire
Wire Stop	Yes
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Electrical Characteristics

Voltage (Max)	600 V
---------------	-------

Body Features

Insulation Material	Nylon
Fully Insulated	No
Quick Disconnect Plating Material	Tin

Contact Features



Terminal Type	Receptacle
Terminal & Splice Type	Receptacle
Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Closed

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	5.84 mm[.23 in]
Overall Length	22.01 mm[.865 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Wire Size	.32 – .82 mm²
Quick Disconnect Mating Tab Width	2.8 mm, 3.18 mm[.11 in][.125 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Flammability Rating	UL 94V-2
UL Rating	Listed

Packaging Features

Packaging Quantity	2000
Quick Disconnect Packaging Method	Strip/Reel

Other

Barrel Color	Red
--------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58628-2
PROCIMP DIESET 26-14 ULTRAFast

TE Part # 90390-3
DIES ULTRA-Fast FASTON 22-18 DIE SET

TE Part # 58628-1
PROCIMP T&D 26-14 ULTRAFast


TE Part # 2-2151698-2
OCEAN_2.0_APPLICATOR-S-FA-176O

TE Part # 2151698-2
OCEAN_2.0_APPLICATOR-S-FA-176O

TE Part # 7-2151698-2
OCEAN_2.0_APPLICATOR-S-FA-176O

TE Part # 7-2151698-7
OCEAN_2.0_SPARE_PART_KIT-176O

Also in the Series | Ultra-Fast 110



Customers Also Bought

TE Part #1-770894-0
3.96mm Wire-to-board housing:
receptacle, with mating alignment, SL
156

TE Part #1971781-2
POWER TRIPLE LOCK REC CONTACT

TE Part #1-1879208-0
CPF 0402 24R 0.1% 25PPM 1K RL

TE Part #2-520193-2
ULTRA-FAST 187 ASY REC 22-18 TPBR

TE Part #2-520405-2
ULTRA-FAST 250 ASY REC 22-18 TPBR

TE Part #1879252-1
RP 2B 4R75 0.1% 15PPM CUT LENGTH

TE Part #1217836-1
HEAVY DUTY BURNER CLIP ST

TE Part #1385303-1
ULTRA POD.250 9SAPR130F210O LM

TE Part #938365P002
VERSAFIT-1/8-0-0.75IN-ST

TE Part #2-1123722-3
3.96 EP PLUG HSG 3P(YELLOW)

Documents

Product Drawings
ULTRA-FAST .110/.125 ASY REC 22-18 TPBR
English

CAD Files
3D PDF
3D
3D PDF
English



Customer View Model

[ENG_CVM_2-520310-2_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_2-520310-2_G.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_2-520310-2_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-520310-2_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-520310-2_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-520310-2_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ultra-Fast and Ultra Fast Plus](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English

[Agency Approval Document](#)

English