



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **1 – 2.5 mm²**

Ring & Spade Stud Size: **#14**

Stud Diameter: **6.5 mm [.24 in]**

Features

Product Type Features

Shape Description	Circular/Oval
Ring & Spade Stud Size	#14
Ring & Spade Barrel Type	Open Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Copper
Support Style	Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Ring & Spade Plating Material	Tin
-------------------------------	-----

Contact Features

Contact Base Material	Phosphor Bronze
Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight
Underplating Material	None



Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.086 – .118 in
Wire Size	1 – 2.5 mm ²
Stud Diameter	6.5 mm[.24 in]
Tongue Thickness	.61 mm[.024 in]
Ring & Spade Overall Length	23.5 mm[.93 in]
Barrel Inside Diameter	1.5 – 1.9 mm[.059 – .075 in]
Ring & Spade Wire Insulation Diameter (Max)	.3 mm[.118 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Ring & Spade Packaging Method	Strip/Reel
-------------------------------	------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2150053-2
OCEAN_2.0_Applicator-E-130F155OV

TE Part # 346101-3
DIN. RING TONGUE TPPHBZ

TE Part # 7-2150053-2
OCEAN_2.0_Applicator-E-130F155OV

TE Part # 7-2150053-7
OCEAN_2.0_SPARE_PART_KIT-130F155OV

Customers Also Bought

TE Part #940590-000
ST63-3-55-22-9

TE Part #CC2621-000
B-106-1501CS100

TE Part #CC2641-000
B-106-3632CS100


TE Part #CC2642-000
B-106-4632CS100

TE Part #CC2628-000
B-106-3631CS100

TE Part #CC2632-000
B-106-8401CS100

TE Part #2823653006
44A0111-12-4

TE Part #CC2637-000
B-106-1802CS100



Documents

Product Drawings

[DIN. RING TONGUE TPPHBZ](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_346103-4_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_346103-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_346103-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English