



Terminals & Splices > PCB Terminals



Terminal & Splice Type: **Tab**

PCB Terminal Terminal Type: **Tab**

PCB Terminal Mating Tab Width: **6.35 mm [.25 in]**

PCB Terminal Mating Tab Thickness: **.81 mm [.032 in]**

PCB Hole Diameter: **2.46 mm [.097 in]**

Features

Product Type Features

FASTON	Yes
PCB Terminal Mounting Style	Stud Mount
Terminates To	Printed Circuit Board

Configuration Features

Stud Hole	Yes
Terminal Angle	90°

Body Features

PCB Terminal Plating Material	Unplated
-------------------------------	----------

Contact Features

Terminal & Splice Type	Tab
PCB Terminal Terminal Type	Tab
Underplating Material	None
Terminal Size	6.35
PCB Terminal Terminal Orientation	Right Angle

Termination Features

PCB Terminal Termination Method	Screw
---------------------------------	-------

Dimensions

Stud Diameter	2.46 mm[.097 in]
PCB Terminal Mating Tab Width	6.35 mm[.25 in]
PCB Terminal Mating Tab Thickness	.81 mm[.032 in]
PCB Hole Diameter	2.46 mm[.097 in]
Height Above PC Board	11.1 mm[.437 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Industry Standards

CSA Certified	Yes
UL Rating	Recognized

Packaging Features

Packaging Quantity	1000
PCB Terminal Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 63274-1
FASTON .250 SERIES (6.3 MM) TAB BR

TE Part # 60080-2
FASTON .250 SERIES (6.3 MM) TAB TPBR

TE Part # 62166-1
FASTON .250 SERIES (6.3 MM) TAB BR

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(143)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(144)

Quick Disconnects(466)

Splices(4)

Customers Also Bought



TE Part #1415015-1
Forced Guided Relay, Reinforced Insulate

TE Part #1-320627-0
PIDG RING TONGUE TERMINALS

TE Part #1-1879450-5
Wirewound Resistor: Mineral, 2.5 Kw

TE Part #1676456-2
RN 0805 8K25 0.1% 10PPM 1KRL

TE Part #1954097-1
Poke In SMT,2 Position Connect

TE Part #103959-7
2X8 MTE RCPT SR LATCH .100CL

TE Part #103960-7
2X8 MTE RCPT SR LATCH .100CL

TE Part #1-456400-9
CRIMPER, WIRE .033 "F"

TE Part #NB20034001
VERSAFIT-1/4-0-SP

TE Part #172775-2
MIC MK-2 REC CONTACT AU

Documents

Product Drawings
250 FASTON,TAB,BR

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_41339_G_c-41339-g.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_41339_G_c-41339-g.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_41339_G_c-41339-g.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON Tabs

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report

English