



EMI Filters > Multi-Function Inlet Filters > CORCOM EF SERIES IEC FILTERED INLETS



Filter Type: **Power Line**

Mount Angle: **Right Angle**

Leakage Current (Max) (120VAC, 60Hz): **210 μ A**

Leakage Current (Max) (250VAC, 50Hz): **360 μ A**

Filter Current Rating: **1 A**

[All CORCOM EF SERIES IEC FILTERED INLETS \(15\)](#)

Features

Product Type Features

Ground Choke Option	No
Ground Option	None
Filter Type	Power Line
Filter Input Termination Type	IEC
Filter Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	210 μ A
Leakage Current (Max) (250VAC, 50Hz)	360 μ A
Filter Current Rating	1 A
Voltage Rating (Max)	250 VAC

Mechanical Attachment

Mount Angle	Right Angle
Filter Mount Style	Flanged

Usage Conditions

Operating Temperature Range	-10 – 40 $^{\circ}$ C
-----------------------------	-----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-EF1
CORCOM EF SERIES IEC FILTERED INLETS



TE Part # 1609142-1
GA400 POWER LINE CO=F6946

Also in the Series | Corcom EF



Multi-Function Inlet Filters(15)


Customers Also Bought



TE Part #1-640456-0
Polyester Vertical PCB Header: 2.54 mm, Unshrouded, No Mating Alignment




TE Part #1735446-3
AMP HPI 2.0MM HEADERS



TE Part #1-1761608-3
IDC LOW PRO HDR 40P VERT SHT L



TE Part #1-640385-8
18P MTA156 HDR ASSY SQ R/A




TE Part #1776146-4
4P TERMI-BLOK HDR,HIGH TEMP




TE Part #T4141412051-000
M12 Panel Mount PCB



TE Part #1734753-1
MINI USB, TYPE B, VERTICAL, T/H



TE Part #1-1658549-6
FPH-2022T=FLXPAC HDR P 20 ST LF



TE Part #1-215300-2
12P HV100 REC CON. TE, 8.5MM,TIN



TE Part #103325-7
07 MODII HDR SRRA B/A .100CL

Documents

Product Drawings

1EF2F=F7322 S0

English

CAD Files

Customer View Model

ENG_CVM_6609015-2_L.3d_igs.zip

English

Customer View Model

1EF2F

Corcom EF, Multi-Function Inlet Filters, Power Line, Right Angle, Leakage Current (Max) (120VAC, 60Hz) 210 µA



[ENG_CVM_6609015-2_L.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_6609015-2_L.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

[1654001_CORCOM_PRODUCT_GUIDE_EF_SERIES](#)

English

Corcom Combined Selector Charts

English