




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **10382 – 26248 CMA**

Ring & Spade Stud Size: **M6**

Features

Product Type Features

Shape Description	D Shaped
Ring & Spade Stud Size	M6
Ring & Spade Barrel Type	Open Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Weight per Piece	3.234 g
Ring & Spade Plating Material	Tin

Contact Features

Contact Base Material	Brass
Terminal & Splice Type	Ring Tongue



Ring & Spade Terminal Orientation	Straight
Underplating Material	None

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.22 in
Wire Size	10382 – 26248 CMA
Stud Diameter	6.73 mm[.26 in]
Tongue Thickness	1.02 mm[.04 in]
Ring & Spade Overall Length	28.19 mm[1.11 in]
Barrel Inside Diameter	3.3 mm, 6.85 mm[.13 in][.27 in]
Ring & Spade Wire Insulation Diameter (Max)	8 mm[.315 in]
Ring & Spade Wire Insulation Diameter	5.59 – 8 mm[.22 – .315 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	110 °C[230 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1500
Ring & Spade Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)



Halogen Content	Does not contain REACH SVHC
Solder Process Capability	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2-2150472-2
OCEAN_2.0_APPLICATOR-E-250F375O



TE Part # 2150472-2
OCEAN_2.0_APPLICATOR-E-250F375O




TE Part # 7-2150472-2
OCEAN_2.0_APPLICATOR-E-250F375O




TE Part # 7-2150472-7
OCEAN_2.0_SPARE_PART_KIT-250F375O

Customers Also Bought



TE Part #1-480281-0
FF 250 REC HSG 6P NYLON BLACK



TE Part #170887-3
IS SHUR PLG 5 DIA NAT




TE Part #2-324485-1
WIRE CAP RED .080-.115



TE Part #170889-2
SLEEVE DIA3 SHUR PLUG NAT






TE Part #102548-1
MOD IV RECP PLTD 15 SEL



TE Part #1544317-1
PC 2V 8MM WP NG1 N




TE Part #2-520128-2
ULTRA-FAST 250 ASY REC 22-18 AWG TPBR



TE Part #1969207-1
ULTRA-POD 250 ASSY REC 18-14 AWG NPST



TE Part #EK5493-000
ES2000-NO.8-A1-0-2IN



TE Part #1393457-3
V23540M1000Z109=BLINDSTOPFEN (

Documents

Product Drawings

RING TONGUE 10-6 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42899-2_AD_c-42899-2-ad.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_42899-2_AD_c-42899-2-ad.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42899-2_AD_c-42899-2-ad.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

ER**Sertissage des Cosses Ref 42899 et 42913

English

Product Environmental Compliance

MD_42899-2_09142017101_dmtec

English



[MD_42899-2_09142017101_dmtec](#)

English

[Agency Approvals](#)

[Agency Approval Document](#)

English