




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **6529 – 10382 CMA**

Ring & Spade Stud Size: **#10**

Features

Product Type Features

Shape Description	Circular/Oval
Ring & Spade Stud Size	#10
Ring & Spade Barrel Type	Open Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Inspection Slot	No
Weight per Piece	1.623 g
Ring & Spade Plating Material	Tin

Contact Features

Contact Base Material	Brass
-----------------------	-------

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight
Underplating Material	None

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.15 in
Wire Size	6529 – 10382 CMA
Stud Diameter	5 mm [.19 in]
Tongue Thickness	.76 mm [.03 in]
Ring & Spade Overall Length	27.18 mm [1.07 in]
Barrel Inside Diameter	3.55 mm, 4.57 mm [.14 in] [.18 in]
Ring & Spade Wire Insulation Diameter (Max)	5.33 mm [.21 in]
Ring & Spade Wire Insulation Diameter	3.81 – 5.33 mm [.15 – .21 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	3000
Ring & Spade Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)

Candidate List Declared Against: JAN 2021
(211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 61844-1
RING TERMINAL 12-10 AWG .0395X.
650 TPCU



TE Part # 150520-2
RT .197 DIA TERMINAL 16-13 AWG
TPBR



TE Part # 2150198-2
OCEAN_2.0_Applicator-E-210F2500



TE Part # 60485-1
RING TERMINAL 14-12 AWG TPBR



TE Part # 280267-2
COSSE RONDE 12 10



TE Part # 42639-1
RING TERMINAL 14-12 AWG BR



TE Part # 2-2150198-2
OCEAN_2.0_Applicator-E-210F2500



TE Part # 60399-1
RING TERMINAL 12-10 AWG TPCU



TE Part # 7-2150198-2
[OCEAN_2.0_Applicator-E-210F2500](#)



TE Part # 7-2150198-7
[OCEAN_2.0_SPARE_PART_KIT-210F2500](#)

Customers Also Bought



TE Part #1-1971876-4
[POWER TRIPLE LOCK STD TEMP PLUG](#)



TE Part #1-1969443-4
[EP 2.5 TPA Retainer, 14 Pos](#)



TE Part #1-520935-5
[PL 250 HOUSING REC BLUE 6/6 NYLON V2](#)



TE Part #1-520935-1
[250 HSG. PL MKII REC. 15.11mm 2P NAT](#)




TE Part #983856-000
[STD SNAP-ON MARKERS](#)



TE Part #2-1624246-8
[RSS3 33R 5% AMMO PK](#)




TE Part #1969608-6
[6P VAL-U-LOK TPA 22-18 AWG](#)



TE Part #1971778-3
[POWER TRIPLE LOCK TPA LOCKING PLATE](#)



TE Part #1969398-2
[POSITIVE LOCK 250 HOUSING RECEPTACLE](#)



TE Part #2-1534798-0
[AMP DUOPLUG 2.5 MK-II 10P SELEC. LOADED](#)

Documents

Product Drawings

[RING .190 \(4.82 MM\) 12-10 AWG TPBR](#)

English

CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_41124_AC_c-41124-ac.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_41124_AC_c-41124-ac.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_41124_AC_c-41124-ac.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Engineering Report

English

Product Environmental Compliance

[MD_41124_12012015213_dmtec](#)

English

[MD_41124_12012015213_dmtec](#)

English

Agency Approvals

UL Report

English