




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**
Wire Size: **13100 – 20800 CMA**
Ring & Spade Stud Size: **M6**

Features

Product Type Features

Shape Description	RING-041
Ring & Spade Stud Size	M6
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Aluminum, Copper
Support Style	Non - Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Weight per Piece	5.525 g
Ring & Spade Plating Material	Tin

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight
Underplating Material	Nickel

Dimensions

Wire Size	13100 – 20800 CMA
-----------	-------------------



Stud Diameter	6.73 mm[.265 in]
Tongue Thickness	1.22 mm[.048 in]
Ring & Spade Overall Length	35.15 mm[1.384 in]
Barrel Inside Diameter	6.05 mm[.238 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-55 – 150 °C[-85 – 347 °F]

Operation/Application

Heavy Duty	No
------------	----

Packaging Features

Packaging Quantity	100
Ring & Spade Packaging Method	Box

Other

Comment	Not approved for reconnection of residential aluminum branch circuit wiring., When two or more wires are used in a parallel splice, the combined cross-sectional area must be within the CMA range listed.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1490572-1
HYP10 COPALUM BAR 8AWG DIE SET



TE Part # 68043
HYP8/10 COPALUM BAR 8AWG DIE SET



TE Part # 68084
HYP8 COPALUM IP 8AWG DIE SET

Customers Also Bought




TE Part #320571
PIDG RING TONGUE TERMINALS



TE Part #31808
TERMINAL,SOLIS R 8 5/16



TE Part #160668-2
110 FASTIN FASTON,REC.,20-16 AWG, PTBR



TE Part #103682-5
06 MTE PANEL MOUNT SR



TE Part #2329384-2
PB OFF/ON FC RED M1 TERM IP68 500MM L



TE Part #1060875-2
MCX CABLE PLUG, CRIMP ATTACH



TE Part #31807
TERMINAL,SOLIS R 8 10



TE Part #1986185-1
Strain Relief,6 Posn,D5200 Dynamic. 2



Documents

Product Drawings

TERMINAL, COPALUM 8 1/4

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_50720-1_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_50720-1_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_50720-1_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

COPALUM Lite Sealed Terminals and Splices

English

Product Specifications

Application Specification

English

COPALUM Terminals And Splices For Solid And Stranded Wire

English

Application Specification

Japanese

Copalum Terminals & Splices f/Solid & Stranded Wire

Japanese

Product Environmental Compliance

TE Material Declaration

English



[Agency Approvals](#)

[UL Report](#)

English