



Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **3.31 – 5.26 mm²**

Quick Disconnect Mating Tab Width: **6.35 mm [.25 in]**

Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire/Cable Type	Regular Wire
Wire Stop	No
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Tin

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle



Quick Disconnect Terminal Orientation	Flag
Contact Base Material	Brass
Crimp Type	Tab-Lok
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
	.04 in
Extraction Force	24.5 Newton
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.79 – 5.33 mm[.11 – .21 in]
Overall Length	17.02 mm[.67 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Wire Size	3.31 – 5.26 mm²
Quick Disconnect Mating Tab Width	6.35 mm[.25 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

CSA Certified	Yes
UL Rating	Listed

Packaging Features

Packaging Quantity	4000
Quick Disconnect Packaging Method	Strip/Reel

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 62056-4 FASTON .250 FLAG REC 18-12 AWG TPBR	TE Part # 62056-3 FASTON .250 SERIES (6.3 MM) FLAG	TE Part # 63617-1 FASTON 250 RECEPTACLE 12-10 AWG BR	TE Part # 61187-1 FASTON 250 FLAG REC 12-10 AWG TPHBZ
TE Part # 1855521-1 HDM/FA/HB EMPO200TL220O LM CUT	TE Part # 687388-6 MHB 9EAPR200T220O G	TE Part # 687389-4 M HBEAPR200T220OK	TE Part # 687389-6 HDM HB 9EMPR200T220O G



TE Part # 565505-2
STD HBEMPR200T220OK

TE Part # 687388-5
M HBEAPR200T220OK

TE Part # 687389-1
M HBEMPO200T220OT

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(143)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(144)

Quick Disconnects(466)

Splices(4)

Customers Also Bought

TE Part #917765-1
Signal Double Lock Tab

TE Part #1376477-6
2.5MM PITCH SIGNAL MATE CONN

TE Part #170466-1
187 FASTON,REC.,18-14 AWG,TPBR


TE Part #170183-1
250 FASTON,REC.,22-18 AWG,BR

TE Part #170183-2
250 FASTON,REC.,22-18 AWG,TPBR

TE Part #1-176497-1
250 HSG. PL EX FLAG REC. NAT

TE Part #170224-2
250 FASTON,REC.,16-10 AWG,BR

TE Part #170213-2
250 FASTON,REC.,18-14 AWG,TPBR



Documents

Product Drawings

FASTON 250 FLAG REC 12-10 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42563-2_DA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_42563-2_DA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42563-2_DA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

AMPLIVAR Bobbin Tab Terminals

English

Application Specification

English

Product Environmental Compliance

MD_42563-2_08202018135_dmtec

English

MD_42563-2_08202018135_dmtec

English

Agency Approvals

UL Report

English

UL Report



English