




Power Triple Lock

TE Internal #: 5-2232266-5

Power Triple Lock, Rectangular Power Connectors, Housing, Plug, Wire-to-Wire, 10 Position, 6mm [.236in] Centerline, Wire & Cable, UL 94V-0

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors > POWER TRIPLE LOCK GLOW WIRE PLUG



Rectangular Power Connector Type: **Housing**
Connector & Housing Type: **Plug**
Connector System: **Wire-to-Wire**
Number of Positions: **10**
Centerline (Pitch): **6 mm [.236 in]**

[All POWER TRIPLE LOCK GLOW WIRE PLUG \(44\)](#)

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	10
Keying	A
Number of Power Positions	10
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------



Contact Features

Contact Layout	Matrix
Contact Retention Within Housing	Without
Contact Type	Receptacle

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	6 mm[.236 in]
Housing Color	Gray
Housing Material	Nylon GF
Cable Exit Angle	Straight

Dimensions

Row-to-Row Spacing	8.1 mm[.319 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 140 °C[-67 – 284 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Identification Marking

Circuit Identification Feature	With
--------------------------------	------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	GWT 750°C (Without Flame)
UL Rating	Recognized
Agency/Standard Number	E28476
VDE Tested	Yes
Agency/Standard	UL, VDE

Packaging Features

Packaging Method	Carton
------------------	--------



Other

For Use With	CPA, Cap Housing, Receptacle (Socket) Contact, TPA
Comment	Complies with IEC 61984 Specification

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # CAT-P87074-R2435 POWER TRIPLE LOCK REC CONTACT	 TE Part # CAT-P87074-T669 POWER TRIPLE LOCK TPA LOCKING PLATE	 TE Part # 1971789-1 CPA	 TE Part # CAT-P87074-P729 POWER TRIPLE LOCK STD TEMP PLUG
---	---	--	--




TE Part # CAT-P87074-C1701B
POWER TRIPLE LOCK: Glow Wire Cap


Also in the Series | Power Triple Lock



Insertion & Extraction Tools(1)



Power Contacts(20)



Rectangular Connector Locking(12)




Rectangular Power Connectors(296)


Customers Also Bought



TE Part #1375820-2
Receptacle Housing: 2.54mm, 1 Row, CST-100 II



TE Part #1971778-5
POWER TRIPLE LOCK TPA LOCKING PLATE



TE Part #180907
FF 250 REC HSG 2P NYLON NAT



TE Part #1971783-1
POWER TRIPLE LOCK REC CONTACT



TE Part #YDTS20Z15-35PNV001
D38999: Square Flange, 15-35 insert



TE Part #170823-9
110 FASTON SLEEVE, REC., TRANSPARENT, NAT



TE Part #1969717-6
HSG, REC., POS-LOCK, MK I 2P, 6.35 SR BLK

Documents

[CAD Files](#)

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_5-2232266-5_B.2d_dxf.zip](#)

[English](#)



Customer View Model

[ENG_CVM_CVM_5-2232266-5_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-2232266-5_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773734-9 TE Power Triple Lock Quick Reference Guide - German](#)

German

[9-1773465-1Power Triple Lock QRG](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[VDE Certificate](#)

English