



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **14**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Header Type	Unshrouded
Rectangular Power Connector Type	Header
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Keying & Polarized Position Locations	4&5, 7&8, 10&11
Number of Positions	14
PCB Mount Orientation	Vertical
Number of Power Positions	14
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------



Contact Features

Contact Layout	Inline
Contact Underplating Material	Nickel
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	7 A
Contact Retention Within Housing	Without
Contact Type	Tab
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	3.81 μm[150 μin]
Contact Termination Area Plating Thickness	2.54 μm[100 μin]

Termination Features

Termination Post & Tail Length	3.24 mm[.128 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Alignment Type	Peg
Strain Relief	Without
Mating Alignment Type	Backwall Interruptions Between Posts
Mating Alignment	With
PCB Mount Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	With
PCB Mount Retention Type	Tab
Connector Mounting Type	Board Mount
Mating Retention	With
Mating Retention Type	Polarized Lock

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
Housing Color	Natural
Housing Material	Polyester - GF

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------



Mating Post Length	11.43 mm[.45 in]
Height	13.84 mm[.545 in]
Length	55.35 mm[2.179 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

CSA Rating	Certified
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire
Agency/Standard Number	E28476
Agency/Standard	CSA, UL
UL Rating	Recognized
CSA File Number	LR7189

Packaging Features

Packaging Method	Bag
Packaging Quantity	400

Other

For Use With	MTA .156 Connector Assembly or SL .156 Connector Assembly
--------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.







Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-103156-WBHSM 3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156	 TE Part # CAT-103156-WBHSN 3.96mm Wire-to-board housing: receptacle, no mating alignment, SL 156	 TE Part # 1-640551-4 14P MTA156 COVER	 TE Part # 1-643071-4 14P MTA156 FD-THRU COVER
 TE Part # 4-640427-4 14P MTA156 CONN ASSY 20AWG YEL	 TE Part # 1-643067-4 14P MTA156 MOLDED COVER	 TE Part # 4-640428-4 14P MTA156 CONN ASSY 22AWG RED	 TE Part # 4-640599-4 14P MTA156 CONN ASSY 18AWG ORA
 TE Part # 4-643818-4 14P MTA156 CONN ASSY 20AWG YEL	 TE Part # 4-640426-4 14P MTA156 CONN ASSY 18AWG ORA	 TE Part # 4-643817-4 14P MTA156 CONN ASSY 18AWG LF	 TE Part # 4-640429-4 14P MTA156 CONN ASSY 24AWG WHT



TE Part # 1-640643-4
14P MTA156 COVER F/T

TE Part # 4-640430-4
14P MTA156 CONN ASSY 26AWG BLU

TE Part # 4-640431-4
14P MTA156 CONN ASSY 18AWG ORA

TE Part # 4-640432-4
14P MTA156 CONN ASSY 20AWG YEL

TE Part # 4-640434-4
14P MTA156 CONN ASSY 24AWG WHT

TE Part # 4-640435-4
14P MTA156 CONN ASSY 26AWG LF

TE Part # 4-640472-4
14C MTA156 ASSY ON TAPE LF

TE Part # 4-640474-4
14P MTA156 ASSY ON TAPE LF

Also in the Series | MTA 156

Insertion & Extraction Tools(1)

PCB Connector Covers(92)

PCB Connector Keying(2)

PCB Connector Mounting(1)

Power Contacts(3)

Rectangular Caps & Covers(1)

Rectangular Power Connectors(748)

Standard Rectangular Connectors (1309)

Wire-to-Board Connector Contacts(12)

Wire-to-Board Headers & Receptacles (729)

Customers Also Bought



TE Part #1558677-6
PCB Power Relay: 30 amp, Monostable DC

TE Part #1-5530841-8
CONN SEC II 30 POS 100C/L

TE Part #1625881-3
1W STD M/OX 2% 270R

TE Part #1625881-4
1W STD M/OX 2% 27R

TE Part #1625881-2
1W STD M/OX 2% 220R

TE Part #966835-3
MOD1 STIFTLEIS 3P

Documents

Product Drawings

14P MTA156 POL HDR ASSY LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_4-644615-4_J.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_4-644615-4_J.3d_igs.zip

English

Customer View Model

ENG_CVM_4-644615-4_J.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_4-644615-4_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-644615-4_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-644615-4_E.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
[MTA, CST-100 II, SL-156 and AMP Economy Power \(EP\) Connectors](#)
English

Product Specifications
[Product Specification](#)
English

Product Environmental Compliance
[MD_4-644615-4_10212011854](#)
English
[MD_4-644615-4_10212011854](#)
English

Agency Approvals
[CSA Certificate](#)
English