




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **.51 – 1.31 mm²**

Quick Disconnect Mating Tab Width: **4.75 mm [.187 in]**

Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Unplated

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle



Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.29 – 3.3 mm[.09 – .13 in]
Overall Length	14.85 mm[.585 in]
Receptacle Terminal Stock Thickness	.3 mm[.012 in]
Wire Size	.51 – 1.31 mm ²
Quick Disconnect Mating Tab Width	4.75 mm[.187 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Rating	Listed
CSA Certified	Yes

Packaging Features

Packaging Quantity	20000
Quick Disconnect Packaging Method	Strip/Reel

Other

Comment	Lock-On
---------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2021
(211)
Candidate List Declared Against: JAN 2021
(211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 63477-2 FASTON .187 RECEPTACLE 20-16 AWG TPBR	 TE Part # 63477-6 FASTON 187 REC 16-20AWG TPPB	 TE Part # 2150007-1 OCEAN_2.0_Applicator-E-090F140F	 TE Part # 91509-1 CCII FASTON 187 REC 20-16 ASSY
 TE Part # 2-2150007-1 OCEAN_2.0_Applicator-E-090F140F	 TE Part # 2-2150007-2 OCEAN_2.0_Applicator-E-090F140F	 TE Part # 2150007-2 OCEAN_2.0_Applicator-E-090F140F	 TE Part # 7-2150007-1 OCEAN_2.0_Applicator-E-090F140F



TE Part # 7-2150007-2
OCEAN_2.0_Applicator-E-090F140F



KIT
TE Part # 7-2150007-7
OCEAN_2.0_SPARE_PART_KIT-090F140F



TE Part # 91509-3
CCII FASTON 187 REC 20-16 HEAD

Also in the Series | FASTON 187



Crimp Terminal Housings(40)



Insertion & Extraction Tools(1)



Joints & Splices(1)



PCB Terminals(48)



Quick Disconnects(222)



Splices(1)

Customers Also Bought



TE Part #1-5645953-2
Mini Spring Sockets: Bullet Nose, 4A



TE Part #292173-9
AMP COMMON TERMINATION HEADERS




TE Part #40723
RING 138(3.50 MM) TERMINAL18-14 AWG TPBR



TE Part #41472
RING TERMINAL 20-16 AWG TPBR




TE Part #40888
RING TERMINAL 20-16 AWG TPBR



TE Part #41343
SPADE 164(4.17MM) 20-16 AWG TPBR



TE Part #42399-1
FASTON 110 TERMINAL REC 20-18 AWG PTPBR



TE Part #284047-6
TERMI-BLOK VERTICAL PLUG STACK



Documents

Product Drawings

FASTON 187 16-20AWG PB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_61939-1_G_c-61939-1-g.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_61939-1_G_c-61939-1-g.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_61939-1_G_c-61939-1-g.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

FASTIN-FASTON 110, 187, 205 And 312 Series Receptacle Contacts

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English