




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**
Wire Size: **.51 – 2.08 mm²**
Quick Disconnect Mating Tab Width: **6.35 mm [.25 in]**
Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Unplated

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle



Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Accepts Wire Insulation Diameter Range	2.16 – 3.43 mm[.085 – .135 in]
Receptacle Terminal Stock Thickness	.3 mm[.012 in]
Wire Size	.51 – 2.08 mm ²
Quick Disconnect Mating Tab Width	6.35 mm[.25 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Rating	Listed
CSA Certified	Yes

Packaging Features

Packaging Quantity	12000
Quick Disconnect Packaging Method	Strip/Reel

Other

Line	Budget
------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)



Halogen Content	Does not contain REACH SVHC
Solder Process Capability	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2-160256-1 250 FASTON,REC.,17-14 AWG,BR	 TE Part # 5-160432-3 FASTON 250 REC 0.5-1.5 MM2 0.40 X63.50 BR	 TE Part # 170183-1 250 FASTON,REC.,22-18 AWG,BR	 TE Part # 41202-1 250 FASTON,REC.,18-14 AWG,BR
 TE Part # 342368-1 187 FASTON,REC.,30-24 AWG,BR	 TE Part # 160807-2 250 FASTON,REC.,20-16 AWG,BR	 TE Part # 160808-2 250 FASTON,REC.,17-14 AWG,BR	 TE Part # 180363-1 250 FASTON,REC.,12-10 AWG,BR
 TE Part # 1-280001-1 250 FASTON,REC.,14-17 AWG,BR	 TE Part # 150645-2 250 FASTON,REC.,18-14 AWG,BR		



Also in the Series | **FASTON 250**

Compression Connectors(4)	Crimp Terminal Housings(143)	Insertion & Extraction Tools(6)	Magnet Wire Terminals(1)
PCB Terminals(144)	Quick Disconnects(466)	Splices(4)	

Customers Also Bought

TE Part #1478762-9 METAL BACKSHELL 9 WAY TOP E	TE Part #170032-2 250 FASTON,REC.,20-14 AWG,BR	TE Part #107129-000 Heat Shrink Boots: Non Lipped, Straight	TE Part #174058-2 MULTILOCK, CONNECTOR HOUSING
TE Part #1534531-1 SIGNAL HEADER	TE Part #1438126-1 50 WAY WIRE SHIELD (PROD)	TE Part #170823-4 250 FASTON SLEEVE,REC., TRANSPARENT	TE Part #1776275-2 Vertical Term Blk Side Wire En
TE Part #184373-1 CONTACT, RECEPTACLE, .070 TYPE	TE Part #HDP24-24-14SN-L017 REC, 14P, BLK, N, RNG, 4/12/16, S		



Documents

Product Drawings

FASTON 250 14-20AWG BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63648-1_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_63648-1_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63648-1_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Wire Preparation And Crimp Inspection Guide

English

Application Specification

English

Agency Approvals

UL Report

English