




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **.51 – 1.31 mm²**

Quick Disconnect Mating Tab Width: **4.75 mm [.187 in]**

Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Low
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Unplated

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle



Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.29 – 3.3 mm[.09 – .13 in]
Receptacle Terminal Stock Thickness	.3 mm[.012 in]
Wire Size	.51 – 1.31 mm ²
Quick Disconnect Mating Tab Width	4.75 mm[.187 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Rating	Listed
CSA Certified	Yes

Packaging Features

Packaging Quantity	16000
Quick Disconnect Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2150007-1 OCEAN_2.0_Applicator-E-090F140F	TE Part # 755336-1 DAHT FASTON 22-14 ASSY	TE Part # 2-2150007-1 OCEAN_2.0_Applicator-E-090F140F	TE Part # 2-2150007-2 OCEAN_2.0_Applicator-E-090F140F
TE Part # 2150007-2 OCEAN_2.0_Applicator-E-090F140F	TE Part # 7-2150007-1 OCEAN_2.0_Applicator-E-090F140F	TE Part # 7-2150007-2 OCEAN_2.0_Applicator-E-090F140F	TE Part # 7-2150007-7 OCEAN_2.0_SPARE_PART_KIT-090F140F

Also in the Series | FASTON 187

Crimp Terminal Housings(40)	Insertion & Extraction Tools(1)	Joints & Splices(1)	PCB Terminals(48)
------------------------------------	--	--------------------------------	--------------------------




Quick Disconnects(222)




Splices(1)


Customers Also Bought



TE Part #1623804-3
Wirewound Resistor: Horizontal Mount



TE Part #GA100K6A11A
DISCRETE 100K OHMS,+/-0.1C 0C TO 70C



TE Part #1586039-6
6P VAL-U-LOK VRT HDR W/P V2



TE Part #1744417-9
9 POS EP 2.5 HSG, GLOW WIRE



TE Part #1-1879350-5
RR01 5% R82 AMMO



TE Part #1-608036-4
SILICONE FUSION TAPE,1"X15'




TE Part #1-643077-4
Nylon PCB Connector Covers: 2.54 mm, MTA 100



TE Part #102316-6
MOD IV RECP PLTD 15 DPLX



TE Part #1-770170-1
03P MINI UMNL ASSY VO SNAU LF



TE Part #1803058-5
ANVIL COMBINATION

Documents

Product Drawings

FASTON 187 RECEPTACLE 20-16 AWG BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63654-1_S_c-63654-1-s.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_63654-1_S_c-63654-1-s.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63654-1_S_c-63654-1-s.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English