




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**
Wire Size: **.51 – 1.31 mm²**
Quick Disconnect Mating Tab Width: **2.8 mm [.11 in]**
Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Tin

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle
Quick Disconnect Terminal Orientation	Straight



Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	3.05 – 3.56 mm [.12 – .14 in]
Overall Length	16.13 mm [.635 in]
Receptacle Terminal Stock Thickness	.25 mm [.01 in]
Wire Size	.51 – 1.31 mm ²
Quick Disconnect Mating Tab Width	2.8 mm [.11 in]
Quick Disconnect Mating Tab Thickness	.81 mm [.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Industry Standards

UL Rating	Listed
CSA Certified	Yes

Packaging Features

Packaging Quantity	12500
Quick Disconnect Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1217003-1
110 FASTON,REC.,18-14 AWG,BR

TE Part # 2-2150384-1
OCEAN_2.0_Applicator-E-070F140F

TE Part # 2-2150384-2
OCEAN_2.0_Applicator-E-070F140FA

TE Part # 2150384-1
OCEAN_2.0_Applicator-E-070F140F

TE Part # 2150384-2
OCEAN_2.0_Applicator-E-070F140FA

TE Part # 7-2150384-1
OCEAN_2.0_Applicator-E-070F140F

TE Part # 7-2150384-2
OCEAN_2.0_Applicator-E-070F140FA

TE Part # 7-2150384-7
OCEAN_2.0_SPARE_PART_KIT-070F140F

Also in the Series | FASTON 110

Crimp Terminal Housings(17)

Insertion & Extraction Tools(1)

PCB Terminals(22)

Quick Disconnects(182)

Customers Also Bought



TE Part #2-326875-4
PIDG RING TONGUE TERMINALS



TE Part #33476
PIDG RECTANGULAR TONGUE TERMINALS



TE Part #HDP24-24-9PE
DEUTSCH HDP20 HOUSINGS




TE Part #185311-1
MQS, CONNECTOR HOUSING



TE Part #1969206-1
ULTRA POD: Straight, Receptacle Assembly, Unplated, .250 inch



TE Part #34152
PG R 22-16 COMM 22-18 MIL 3/8



TE Part #160915-2
250 FASTON,REC.,20-17 AWG,TPPB



TE Part #1742350-1
PIN 2.08 DIA 22-18AWG TPBR



TE Part #5-1241961-8
3POS STD-TIMER HOUSING PITCH5 MK II



TE Part #2035366-7
AMPSEAL 16 BACKSHELLS

Documents

Product Drawings

FASTON .110 RECEPTACLE 20-16 AWG PTPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63703-1_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_63703-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63703-1_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Application Specification

English

Wire Preparation And Crimp Inspection Guide

English

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report

English