




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Spade Tongue**

Wire Size: **1021 – 2582 CMA**

Ring & Spade Stud Size: **#6, M3.5**

Features

Product Type Features

Shape Description	Square Spade
Ring & Spade Stud Size	#6, M3.5
Ring & Spade Barrel Type	Open Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Ring & Spade Plating Material	Tin
-------------------------------	-----

Contact Features

Contact Base Material	Brass
Terminal & Splice Type	Spade Tongue
Ring & Spade Terminal Orientation	Straight
Underplating Material	None



Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.1 in
Wire Size	1021 – 2582 CMA
Stud Diameter	3.51 mm[.138 in]
Tongue Thickness	.51 mm[.02 in]
Ring & Spade Overall Length	19.05 mm[.75 in]
Barrel Inside Diameter	1.52 mm, 2.92 mm[.06 in][.115 in]
Ring & Spade Wire Insulation Diameter (Max)	3.56 mm[.14 in]
Ring & Spade Wire Insulation Diameter	2.54 – 3.56 mm[.1 – .14 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	11000
Ring & Spade Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 61498-2
SPADE 28-22 AWG .0157 X .310 TPBR

TE Part # 60390-1
SPADE CRIMP 20-16 AWG BR

TE Part # 2-4150040-2
OCEAN-2.0-APPLICATOR-E-110F1550

TE Part # 61498-3
SPADE IP 22-28 133 016PTPBR

TE Part # 7-4150040-2
OCEAN-2.0-APPLICATOR-E-110F1550

TE Part # 7-4150040-7
OCEAN_2.0_SPARE_PART_KIT-110F1550

TE Part # 4150040-2
OCEAN-2.0-APPLICATOR-E-110F1550

TE Part # 466211-2
HDM EMPR110F155OK A

Customers Also Bought

TE Part #1-643075-1
Nylon PCB Connector Covers: 2.54 mm, MTA 100

TE Part #1217050-1
187 FASTON,TAB,TPBR

TE Part #1393117-8
KUP-1D55-24=KU

TE Part #927766-1
TIMER, RECEPTACLE AND TAB





TE Part #175061-1
MULTILOCK, RECEPTACLE AND TAB



TE Part #1217330-1
RING TONGUE 16-14 AWG TPBR




TE Part #103759-5
05 MODII HDR SRRA B/A .100CL



TE Part #1673255-3
HOLDER, REAR SHEAR



TE Part #1673257-7
SHEAR, FLOATING



TE Part #1742348-1
9 Serr AMPLIVAR Spade

Documents

Product Drawings

ST .138 DIA TERMINAL 20-16 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60389-2_P_c-60389-2-p.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_60389-2_P_c-60389-2-p.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60389-2_P_c-60389-2-p.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Engineering Report

English